





KLEENGUARD* A40 Liquid & Particle Protection Coveralls & Accessories

Product Information


Zipper Front	Vending		Size	Qty
	Code	Machine Ready		
	27151 [‡]	42568	S	25
	44302	42569	M	25
	44303	37685	L	25
	44304	37886	XL	25
	44305	37837	2XL	25
	44306	37692	3XL	25
	44307	37694	4XL	25
	30922 [‡]	42570	5XL	25
	30927 [‡]	42571	6XL	25

Zipper Front, Elastic Wrists & Ankles	Vending		Size	Qty
	Code	Machine Ready		
	30905 [‡]	No	S	25
	44312	No	M	25
	44313	37695	L	25
	44314	37696	XL	25
	44315	37701	2XL	25
	44316	37702	3XL	25
	44317	37703	4XL	25
	30904 [‡]	No	5XL	25
	27189 [‡]	No	6XL	25
	35630 [‡]	No	5XL/6XL	25


Zipper Front, Elastic Wrist, Ankles & Hood	Vending		Size	Qty
	Code	Machine Ready		
	30940 [‡]	42564	S	25
	44322	42565	M	25
	44323	42566	L	25
	44324	41172	XL	25
	44325	41173	2XL	25
	44326	41174	3XL	25
	44327	42567	4XL	25
	27158 [‡]	No	5XL	25
	30921 [‡]	No	6XL	25

Zipper Front, Elastic Wrists, Ankles, Hood & Boots	Code	Size	Qty
		30939 [‡]	S
44332		M	25
44333		L	25
44334		XL	25
44335		2XL	25
44336		3XL	25
44337		4XL	25
30907 [‡]		5XL	25
30934 [‡]		6XL	25


Product Information

Lab Coat	Code	Size	Qty
	35617 [‡]	XS	30
	27201 [‡]	S	30
	44452	M	30
	44453	L	30
	44454	XL	30
	44455	2XL	30
	44456	3XL	30
	27207 [‡]	4XL	30
	30935 [‡]	5XL	30

- 4 snap closure
- Open Wrists
- Knee length
- Left chest pocket
- Right hip pocket
- White

Lab Coat	Code	Size	Qty
	30938 [‡]	S	30
	44442	M	30
	44443	L	30
	44444	XL	30
	44445	2XL	30
	44446	3XL	30
	30923 [‡]	4XL	30
	30941 [‡]	5XL	30


- 5 snap closure
- Elastic Wrists
- Knee length
- No pocket
- White

Shirt	Code	Size	Qty
	44402	M	50
	44403	L	50
	44404	XL	50
	44405	2XL	50

- 5 snap closure
- Hip length
- No pocket
- White

Apron	Code	Size	Qty
	44481	28"x40"	100

- Bound Neck & Ties
- White
- One Size fits all


Pants	Code	Size	Qty
	44412	M	50
	44413	L	50
	44414	XL	50
	44415	2XL	50

- Elastic Waist
- Open ankle
- White


*Made-to-order Codes


KLEENGUARD* A40 Liquid & Particle Protection Coveralls & Accessories – Continued

Product Information – cont'd


Sleeve Protector	Vending		Size	Qty
	Code	Machine Ready		
 <ul style="list-style-type: none"> Elastic top & Wrists 18" Length White 	44480	41175	18"	200

Boot Cover	Code	Size	Qty
 <ul style="list-style-type: none"> Elastic opening 17" height Seamless sole White One size fits all 	44491	Universal	400

Boot Cover	Code	Size	Qty
 <ul style="list-style-type: none"> Elastic top Elastic at ankle Highly durable PVC sole 18" height White 	36779	M/L	400
	44495	XL/2XL	400

Shoe Cover	Code	Size	Qty
 <ul style="list-style-type: none"> Elastic opening 7" height Seamless sole White One size fits all 	27000	Universal	300

Shoe Cover	Code	Size	Qty
 <ul style="list-style-type: none"> Fully elasticized for formed fit 7" height White One size fits all 	44490	Universal	400

Shoe Cover	Code	Size	Qty
 <ul style="list-style-type: none"> Elastic Top Highly durable PVC sole 5.25" height White 	44492	M/L	400
	44494	XL/2XL	400

Fabric Properties

Physical Properties	Test Methods	Target
Tensile Strength (MD)	ASTM D5034	30.6 lbs.
Tensile Strength (CD)	ASTM D5034	21.4 lbs.
Trapezoidal Tear (MD)	INDA IST 100.2	11.0 lbs.
Trapezoidal Tear (CD)	INDA IST 100.2	7.2 lbs.
Elongation (MD)	ASTM D5034	72%
Elongation (CD)	ASTM D5034	89%
Lint -#of particles [†] >0.5µm	INDA 160.1-92	761
Flammability	CPSC 1610	Class 1
Static Decay (<0.5 secs.)	NFPA 99	Pass

[†]Benchmark testing, sample = 1

Barrier Properties	Test Methods	Target
Hydrohead	AATCC 127-1998	187 cm
Particle Holdout (0.3-0.5 µm)	Independent Lab	99.999%
Blood Penetration	ASTM F1670	Pass
Protects against Potassium Chromate (20%)	ASTM F903-10	Pass
Protects against Isocyanates [‡]	ASTM F903-10	Pass

[‡]Tested against polyurethane containing polymeric isocyanate (40% concentration)

Additional Attributes

Microporous film laminate
Product not made with silicone
Not made with BHT preservative
Not made with natural rubber latex
Meets ANSI/ISEA 101-1996 sizing standards
Serged seams

Workmanship Requirements:

All coveralls and accessories shall be made in accordance with reasonable industry practice with respect to holes, tears, wrinkles, cleanliness, and foreign materials or dirt.

For Additional information: Contact your Kimberly-Clark representative, our Customer Service Team (888)-346-GOKC (4652) or KCPInfo@kcc.com