

## Improved!

# Model 300 Complete Threading System

The RIDGID 300 Power Drive is a proven workhorse and has been the backbone of thousands of job sites across the country for almost 50 years. To make on-site threading even easier, Ridge Tool offers the 300 Complete that includes everything you need to make threads quickly and easily in the field or in your shop. The 300 Complete offers versatility and function of quick tear down and easy transportation to be able to go wherever you need to go.

From the heavy-duty foot switch, solid 1206 stand, robust all-weather 418 oiler, and the redesigned removable tool tray, the RIDGID 300 Complete provides the ultimate in threading form and function. Already have an award winning RIDGID 300 Power Drive, simply add the necessary accessories and create your own 300 Complete Threading System!



#1452 Tray



### Technical Specifications


- Motor:** 1/2 HP, Universal reversible motor, single-phase, 25-60 HZ
- Switch:** Heavy-duty FOR/OFF/REV and Integral Foot Switch
- Chuck:** RIDGID speed chuck with replaceable rocker-action jaws
- Spindle Speed:** 38 RPM (57 RPM available)
- Rear Centering Device:** Cam-action turns with chuck
- Support Bar:** Heavy-duty (2)

### Ordering Information

Catalog No.	Model No.	Description	Spindle Speed RPM	Pipe Threading Capacity		Rod Threading Capacity		Maximum Geared Threader Capacity		Weight	
				In.	mm	in.	mm	in.	mm	lbs	kg
15682	300 Complete	115V, 25-60 Hz (NPT)	38	1/8 - 2	3 - 50	1/4 - 2	6 - 50	6	150	218	96.2
15722	300 Complete	115V, 25-60 Hz (NPT)	57	1/8 - 2	3 - 50	1/4 - 1 1/2	6 - 40	6	150	218	96.2

### Model 300 Power Drive Complete Consists of:

- 300 Power Drive with Foot Switch
- Set 1/2" - 3/4" Universal Alloy Dies
- Set 1" - 2" Universal Alloy Dies
- 311 Carriage with Lever
- 811A Universal Die Head
- 32 Transporter
- 1452 Removable Tray
- 1206 Stand
- Reamer
- 360 Cutter
- 418 Oiler
- 1 Gallon Nu-Clear Thread Cutting Oil



#32 Transporter

### Accessories

Catalog No.	Model No.	Description	Weight	
			lbs	kg
42360	1206	Stand for 300 power Drive	31	14.1
42575	32	Transporter (for Power Drives and Tri-stand Vises)	14 1/4	6.5
68815	311	Carriage with No. 312 Lever	15	6.8
10883	418	Oiler with 1 Gallon of Nu-Clear Thread Cutting Oil	20 1/2	9.4
42365	341	Reamer for No. 311 Carriage	7	3.2
42370	360	Cutter for No. 311 Carriage	8 1/2	3.9
97065	811A	Universal Q.O. Die Head Only, Right Hand Only	12 1/2	5.7
97075	815A	Self-Opening Die Head Only, Right Hand Only	13 1/2	6.1
51005	819	Nipple Chuck Complete, 1/2" - 2" (12mm - 50mm)	10 1/2	4.8
42380	1452	Removable Tool Tray	6	2.7
46660	E-863	LH/RH Reamer Cone	7	3.2