

Previously known as: MICROCHEM® by AlphaTec® 1500 - Model 103

Provides comfortable protection from particulates and light, non-flammable liquid spray or splash.

- Flame retardant and anti-static SMMS nonwoven provides a good barrier to particulates and low hazard liquid sprays or splashes
- Air and water vapour permeable (breathable) to help reduce the risk of heat stress
- Optimised body fit ensures full freedom of movement when worn over heat and flame protective clothing (EN ISO 14116 Index 2 or above)
- Anti-static, tested according to EN 1149-5 and AATCC 76

Industries

- Oil and gas
- Chemical

Applications

- General pumping work
- Preparation of site - set-up and disassembly of tool string
- Environmental clean-up and remediation
- Warehousing of raw materials
- Chemical Handling



AlphaTec®

ADVANCED CHEMICAL PROTECTION

1500 PLUS FR - Model 103

Breathable, anti-static, Flame Retardant SMS material, Type 5/6 protection

Previously known as: MICROCHEM® by AlphaTec® 1500 - Model 103

PRODUCT INFORMATION

Product Material	SMMS fabric with fire retardant and anti-static treatment
Design Features	Coverall with collar, 2-way front zipper with DST storm flap and finger loops. Elasticated wrists, waist and ankles. Red stitching for ease of identification.
Seam Type	Stitched seams
Standards Overview	CE CATEGORY III (Type 5, Type 6, EN 1073-2, EN ISO 14116, EN 1149-5/AATCC 76)
Product Reference	1500 PLUS FR - Model 103
Country Of Origin	China
Sizes	S-5XL (02-09)
Weight	54gsm

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306.
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2019 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.