



T5 Standard

F14T5/841/ALTO 40PK

Philips T5 Fluorescent Lamps featuring ALTO® Lamp Technology offer increased energy savings and low toxicity in a slim profile.

Warnings and Safety

· Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information		Color Rendering Index (Min)	
Base	G5 [G5]	Color Rendering Index (Nom)	82
Life to 50% Failures Preheat (Nom)	24000 h	LLMF 2000 h Rated	96 %
Features	HE Alto® [High Efficiency Alto]	LLMF 4000 h Rated	95 %
System Description	High Efficiency	LLMF 6000 h Rated	94 %
LSF Preheat 2000 h Rated	99 %	LLMF 8000 h Rated	93 %
LSF Preheat 4000 h Rated	99 %	LLMF 12000 h Rated	92 %
LSF Preheat 6000 h Rated	99 %	LLMF 16000 h Rated	91 %
LSF Preheat 8000 h Rated	99 %	LLMF 20000 h Rated	90 %
LSF Preheat 16000 h Rated	97 %		
LSF Preheat 20000 h Rated	84 %		
Light Technical		Operating and Electrical	
Color Code	841 [CCT of 4100K]	Power (Rated) (Nom)	14.0 W
Initial lumen (Nom)	1350 lm	Lamp Current (Nom)	0.165 A
Luminous Flux (Rated) (Nom)	1200 lm		
Color Designation	Cool White (CW)	Temperature	
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	99 lm/W	Design Temperature (Nom)	35 °C
Correlated Color Temperature (Nom)	4100 K		
Luminous Efficacy (rated) (Nom)	86 lm/W	Controls and Dimming	
Color Rendering Index (Max)	85	Dimmable	Yes
		Mechanical and Housing	
		Cap-Base Information	Green [Green Cap]

T5 Standard

Bulb Shape	T5 [16 mm (T5)]
Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	14W/841 Min Bipin T5 HE ALTO UNP/40

EAN/UPC - Product	046677230807
Order code	230805
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927990484022
Net Weight (Piece)	54.000 g
ILCOS Code	FDH-14/40/1B-L/P-G5-16


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
14W/841 Min Bipin T5 HE	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm
ALTO UNP/40					

TL5 HE F14T5/841 HE Alto

Lifetime



LDLE_TL5-HE8_0001-Life expectancy diagram



LDLE_TL5-HE8_0002-Life expectancy diagram

T5 Standard

Lifetime



LDLM_TL5-HE8_0001-Lumen maintenance diagram

