



Grainger Stock No.	Item	Type	SAE or Metric	Number of Pieces	Drive Size	Finish	Included	Accessories	Meets / Exceeds
4LWZ7	Socket Set	12 Pt Std, 12Pt Deep	SAE	32	1/2	Full Polished Chrome Plating	12 Pt Std : 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1, 1-1/16, 1-1/8, 1-1/4" 12 Pt Deep : 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1, 1-1/16, 1-1/8, 1-1/4"	Pear Head Ratchet, 5 and 10" Extensions, 16" Flexible Handle, Metal Box	ASME B107.10M-1996 ASME B107.1-2002
4LWZ8	Socket Set	6 Pt Std, 12Pt Std, 12Pt Deep	SAE	26	1/2	Full Polished Chrome Plating	6 Pt Std : 7/16, 1/2, 9/16, 5/8, 11/16, 3/4 12 Pt Std : 13/16, 7/8, 15/16, 1, 1-1/16, 1-1/8, 1-1/4 12 Pt Deep : 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1	Pear Head Ratchet, 5" Extensions, Universal Joint, 16" Flexible Handle, Blow Mould Case	ASME B107.10M-1996 ASME B107.1-2002
4LWZ9	Socket Set	12 Pt Std, 12Pt Deep	SAE	22	3/8	Full Polished Chrome Plating	12 Pt Std : 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8 12 Pt Deep : 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8	Pear Head Ratchet, 3 and 6" Extensions, Universal Joint, Metal Box	ASME B107.10M-1996 ASME B107.1-2002
4LXA1	Socket Set	6 Pt Std, 6Pt Deep	SAE	22	3/8	Full Polished Chrome Plating	6 Pt Std : 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8 6 Pt Deep : 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8	Pear Head Ratchet, 3 and 6" Extensions, Universal Joint, Metal Box	ASME B107.10M-1996 ASME B107.1-2002
4LXA2	Socket Set	6 Pt Std,	SAE	18	1/2	Full Polished Chrome Plating	6 Pt Std : 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1, 1-1/16, 1-1/8, 1-3/16, 1-1/4"	Pear Head Ratchet, 5" Extensions, 16" Flexible Handle, Metal Box	ASME B107.10M-1996 ASME B107.1-2002
4LXA3	Socket Set	6 Pt Std,	SAE	22	1/4, 3/8	Full Polished Chrome Plating	1/4"Dr: 6 Pt Std: 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8 3/8"Dr: 6 Pt Std: 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1	1/4"Dr: Spinner Handle 3/8"Dr: Pear Head Ratchet, 3 and 6" Extensions, 3/8"F*1/4"M Adapter, Metal Box	ASME B107.10M-1996 ASME B107.1-2002
4LXA4	Socket Set	12 Pt Std, 12Pt Deep	SAE	25	1/4	Full Polished Chrome Plating	12 Pt Std : 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2, 9/16 12 Pt Deep : 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2, 9/16	Pear Head Ratchet, 2 and 6" Extensions, Spinner Handle, Universal Joint, Metal Box	ASME B107.10M-1996 ASME B107.1-2002
4LXA5	Socket Set	12 Pt Std,	SAE	18	1/2	Full Polished Chrome Plating	12 Pt Std : 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1, 1-1/16, 1-1/8, 1-3/16, 1-1/4"	Pear Head Ratchet, 5" Extensions, 16" Flexible Handle, Metal Box	ASME B107.10M-1996 ASME B107.1-2002
4LXA6	Socket Set	12 Pt Std,	SAE	26	1/2	Full Polished Chrome Plating	12 Pt Std : 3/8, 7/16, 1/2, 9/16, 19/32, 5/8, 21/32, 11/16, 3/4, 25/32, 13/16, 7/8, 15/16, 31/32, 1, 1-1/16, 1-1/8, 1-3/16, 1-1/4"	Pear Head Ratchet, 3, 5 and 10" Extensions, Universal Joint, 16" Flexible Handle, 16-1/2" Speeder Handle, Blow Mould Case	ASME B107.10M-1996 ASME B107.1-2002
4LXA7	Socket Set	6 Pt Std, 6Pt Deep, 8 Pt Std	SAE	37	1/4	Full Polished Chrome Plating	6 Pt Std : 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2, 9/16 6 Pt Deep : 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2, 9/16 8 Pt Std : 1/4, 5/16, 3/8 Ph Bit Skt : #1, #2 Hex Bit Skt : 5/32, 3/16, 1/4	Pear Head Ratchet, 2, 3 and 6" Extensions, Spinner Handle, Universal Joint, Flexible Handle, Sliding T Bar, Spring Extension Bar, Metal Box	ASME B107.10M-1996 ASME B107.1-2002
4LXA8	Socket Set	6 Pt Std, 6Pt Deep	SAE	25	1/4	Full Polished Chrome Plating	6 Pt Std : 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2, 9/16 6 Pt Deep : 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2, 9/16	Pear Head Ratchet, 2 and 6" Extensions, Spinner Handle, Universal Joint, Metal Box	ASME B107.10M-1996 ASME B107.1-2002
4LXA9	Socket Set	12 Pt Std, 12Pt Deep 8 Pt Std,	SAE	33	3/8	Full Polished Chrome Plating	12 Pt Std : 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 12 Pt Deep : 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 8 Pt Std : 1/4, 5/16, 3/8 UJ SKT : 7/16, 1/2, 9/16, 5/8, 3/4	Pear Head Ratchet, 3, 6 and 10" Extensions, Universal Joint, 10" Flexible Handle, 14-1/2" Speeder Handle, Blow Mould Case	ASME B107.10M-1996 ASME B107.1-2002
4LXC1	Socket Set	6 Pt Std,	SAE	12	3/8	Full Polished Chrome Plating	6 Pt Std : 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8,	Pear Head Ratchet, 3 and 6" Extensions, Metal Box	ASME B107.10M-1996 ASME B107.1-2002
4LXC2	Socket Set	6 Pt Std, 6Pt Deep 12 Pt Std	SAE Metric	27	1/4	Full Polished Chrome Plating	12 Pt Std : 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2 6 Pt Deep : 1/4, 9/32, 5/16, 11/32, 3/8, 7/16 6 Pt Std : 4, 5, 6mm 12 Pt Std : 7, 8, 9, 10, 11, 12, 13mm	Pear Head Ratchet, 3" Extensions, Blow Mould Case	ASME B107.10M-1996 ASME B107.5M-2002 ASME B107.1-2002
4LXC3	Socket Set	12Pt Deep	SAE	15	1/2	Full Polished Chrome Plating	12 Pt Deep : 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1, 1-1/16, 1-1/8, 1-3/16, 1-1/4"	Socket Rail	ASME B107.1-2002
4LXC4	Socket Set	6Pt Deep	SAE	15	1/2	Full Polished Chrome Plating	6 Pt Deep : 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1, 1-1/16, 1-1/8, 1-3/16, 1-1/4"	Socket Rail	ASME B107.1-2002
4LXC5	Socket Set	12Pt Deep	SAE	16	1/2	Full Polished Chrome Plating	12 Pt Deep : 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1, 1-1/16, 1-1/8, 1-3/16, 1-1/4, 1-1/2	Socket Rail	ASME B107.1-2002
4LXC6	Socket Set	12 Pt Std,	Metric	15	1/2	Full Polished Chrome Plating	12 Pt Std : 10, 11, 12, 13, 14, 15, 17, 18, 19, 21, 22, 24, 27, 30, 32mm	Socket Rail	ASME B107.5M-2002
4LXC7	Socket Set	12Pt Deep	SAE	11	1/2	Full Polished Chrome Plating	12 Pt Deep : 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1, 1-1/16, 1-1/8	Socket Rail	ASME B107.1-2002
4LXC8	Socket Set	12 Pt Std,	Metric	17	1/2	Full Polished Chrome Plating	12 Pt Std : 10, 11, 12, 13, 14, 17, 19, 22, 23, 24, 25, 26, 27, 28mm	Pear Head Ratchet, 5 Extensions, 16 Flexible Handle, Blow Mould Case	ASME B107.10M-1996 ASME B107.5M-2002
4LXC9	Socket Set	12Pt Deep	SAE	9	3/8	Full Polished Chrome Plating	12 Pt Deep : 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8	Socket Rail	ASME B107.1-2002
4LXD1	Socket Set	6Pt Deep	SAE	12	1/2	Full Polished Chrome Plating	6 Pt Deep : 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1	Socket Rail	ASME B107.1-2002
4LXD2	Socket Set	12 Pt Std,	SAE	12	1/2	Full Polished Chrome Plating	12 Pt Std : 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1	Pear Head Ratchet, 5 Extensions, Blow Mould Case	ASME B107.10M-1996