

Stamped

Each Stamped Steel Cutlery product has been engineered by Klein Cutlery and manufactured to our exact standards to ensure the highest quality. The precision ground, high quality stainless steel blades, offer a lightweight option but still produce a sharp, clean, uniform cut. The ergonomic designs allow for accuracy, comfort and performance. Cutting blades are held together by a unique locking nut and bolt design. This provides adjustable blade tension needed to maintain optimum cutting performance. All handles are designed for comfort and built for ambidextrous use.

Bent



Straight



Utility



Stamped

5" Straight Trimmer

- Double sharp points for hard-to-reach areas.
- Ideal for detail work.

7135



Cat. No.	Blade Curvature	Blade Edge	Blade Material	Blade Tip	Handed	Handle Material	Handle Orientation	Length of Cut	Overall Length
7135	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Straight	2"	5 1/8"
7135MT	Straight	Standard	Stainless Steel	Micro Tip	Ambidextrous	Molded Plastic	Straight	2"	5 1/8"
*7135P	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Straight	2"	5 1/8"

* Available in Packaging

6-5/8" Straight Trimmer

- Double sharp points for hard-to-reach areas.
- Ideal for detail work.

7165



Cat. No.	Blade Curvature	Blade Edge	Blade Material	Blade Tip	Handed	Handle Material	Handle Orientation	Length of Cut	Overall Length
7165	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Straight	2 1/2"	6 1/2"

8" Bent Trimmer

- Lightweight Tool.
- Cuts multiple layers of cloth, canvas, and string.

9208



Cat. No.	Blade Curvature	Blade Edge	Blade Material	Blade Tip	Handed	Handle Material	Handle Orientation	Length of Cut	Overall Length
9208	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent	3 3/8"	8 1/4"
*9208P	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent	3 3/8"	8 1/4"

* Available in Packaging

9" Straight Trimmer

- Lightweight cutting tool.
- Great for various cutting applications.
- Stainless steel blades.

7158



Cat. No.	Blade Curvature	Blade Edge	Blade Material	Blade Tip	Handed	Handle Material	Handle Orientation	Length of Cut	Overall Length
7158	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Straight	3 1/4"	8 1/8"
7159	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Straight	3 1/2"	9"
7159BP	Straight	Standard	Stainless Steel	Ball Point	Ambidextrous	Molded Plastic	Straight	3"	9"

Stamped

8" Bent Aramid Fiber Shear

- Rockwell 62C making it ideal for Kevlar®.
- Powerful cutting capabilities.
- Large ring handle for added cutting leverage.

8217LR



Cat. No.	Blade Curvature	Blade Edge	Blade Material	Blade Tip	Handed	Handle Material	Handle Orientation	Length of Cut	Overall Length
8217LR	Straight	Serrated	Stainless Steel	Sharp	Right	Molded Plastic	Bent	2 5/8"	8"

Kevlar® is a registered trademark of E.I. du Pont de Nemours and Company.

8" Bent Trimmer

- Cat. No. 7210 models have slightly rounded top blade lets material fall away with no snagging.
- Soft, regular size blue handles.
- Cat. No. 7211 models are excellent for tabletop work.

7210



Cat. No.	Blade Curvature	Blade Edge	Blade Material	Blade Tip	Handed	Handle Material	Handle Orientation	Length of Cut	Overall Length
7210	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent	3 3/8"	8 3/8"
7210C	Curved	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent	3 3/8"	8 3/8"
*7210P	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent	3 3/8"	8 3/8"
7210BK	Straight	Knife	Stainless Steel	Blunt	Ambidextrous	Molded Plastic	Bent	3 1/4"	8 1/8"
7210BP	Straight	Standard	Stainless Steel	Ball Point	Ambidextrous	Molded Plastic	Bent	3 1/4"	8 1/8"
7211	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent	3 3/8"	8 3/8"

* Available in Packaging

9" Bent Trimmer

- Extra large bottom ring for comfort.
- Less strain on wrist and hand.
- Excellent for glove use and wet applications.
- Cat. No. 7221 both tips are sharp.
- Cat. Nos. 7222 & 7224 have black handles and stainless nonstick finish.

7220



Cat. No.	Blade Curvature	Blade Edge	Blade Material	Blade Tip	Handed	Handle Material	Handle Orientation	Length of Cut	Overall Length
7220	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent	3 3/8"	8 7/8"
7220BP	Straight	Standard	Stainless Steel	Ball Tip	Ambidextrous	Molded Plastic	Bent	3"	8 3/4"
7220C	Curved	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent	3 3/8"	8 7/8"
7220N	Straight	Notched	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent	2 1/4"	8 7/8"
7220K	Straight	Standard	Stainless Steel	Knife	Ambidextrous	Molded Plastic	Bent	3 3/8"	8 7/8"
7222	Straight	Standard	Stainless Nonstick Finish	Sharp	Ambidextrous	Molded Plastic	Bent	3 3/8"	8 7/8"
7224	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent	3 3/8"	8 7/8"

9" Bent Trimmer

- Excellent for tabletop work.
- Sharp Tipped Bent Trimmer.
- Extra large bottom ring for comfort.

7221



Cat. No.	Blade Curvature	Blade Edge	Blade Material	Blade Tip	Handed	Handle Material	Handle Orientation	Length of Cut	Overall Length
7221	Straight	Standard	Stainless Nonstick finish	Sharp	Ambidextrous	Molded Plastic	Bent	3 3/8"	8 7/8"

Stamped

9" Self Opening Bent Trimmer

- Caiman Poultry Shear (7231) is engineered to be both durable enough for deboning yet precise enough for detailed work including trimming of thighs, wings and breasts.
- Exclusive Straight Top Handle Design to reduce Operator fatigue
- PolyMag Infused Nylon Spring for added safety and processing quality assurance.
- Self Opening Design with Replaceable Spring.
- Ergonomic Ambidextrous Handle Design.



Cat. No.	Blade Curvature	Blade Edge	Blade Material	Blade Tip	Handed	Handle Material	Handle Orientation	Length of Cut	Overall Length
7231	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent - Self Opening	3 1/2"	9 3/4"
7231BP	Straight	Standard	Stainless Steel	Ball Point	Ambidextrous	Molded Plastic	Bent - Self Opening	3 1/4"	9 3/4"
7231C	Curved	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent - Self Opening	3 1/2"	9 3/4"
7231S	Straight	Serrated	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent - Self Opening	3 1/2"	9 3/4"

9-1/2" Bent Trimmer

- Extra large Ergo bottom handle.
- Similar to the 7220 model but has longer cut length.



Cat. No.	Blade Curvature	Blade Edge	Blade Material	Blade Tip	Handed	Handle Material	Handle Orientation	Length of Cut	Overall Length
7240	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent	4"	9 1/2"
7240BP	Straight	Standard	Stainless Steel	Ball Point	Ambidextrous	Molded Plastic	Bent	3 3/4"	9 1/2"
7240C	Curved	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent	3 3/4"	9 1/2"
7240N	Straight	Notched	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent	2 3/4"	9 1/2"
*7240P	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent	3 3/4"	9 1/2"

* Available in Packaging

9-1/2" Ergo Shear With Strap

- Self opening spring makes this truly an ergonomic tool.
- Great for repetitive cutting jobs.
- Well balanced to reduce fatigue.
- Replacement straps available; Item #7241X.



Cat. No.	Blade Curvature	Blade Edge	Blade Material	Blade Tip	Handed	Handle Material	Handle Orientation	Length of Cut	Overall Length
7241	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent - Self Opening	4"	9 1/2"
7241C	Curved	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent - Self Opening		
7241BP	Straight	Standard	Stainless Steel	Ball Point	Ambidextrous	Molded Plastic	Bent - Self Opening		

11" Heavy Duty Bent Trimmer

- Soft blue handle with extra large bottom ring that allows the operator to cut for long periods of time without the usual cramping of the hands!
- Can be used right or left handed.
- Extended cut length.



Cat. No.	Blade Curvature	Blade Edge	Blade Material	Blade Tip	Handed	Handle Material	Handle Orientation	Length of Cut	Overall Length
7310	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent	4 3/4"	11"
*7310P	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent	4 3/4"	11"
7310BP	Straight	Standard	Stainless Steel	Ball Point	Ambidextrous	Molded Plastic	Bent	4 1/4"	11"

Stamped

12" Bent Trimmer

- Soft blue handle with extra large bottom ring that allows the operator to cut for long periods of time without the usual cramping of the hands!
- Extended cut length.

7312



Cat. No.	Blade Curvature	Blade Edge	Blade Material	Blade Tip	Handed	Handle Material	Handle Orientation	Length of Cut	Overall Length
7312	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Bent	5/8"	5"

8" Pinking Scissor

- Sawtoothed blade that leaves a zigzag pattern instead of a straight edge.
- Cuts woven cloth.

N5350



N5350



Cat. No.	Blade Curvature	Blade Edge	Blade Material	Blade Tip	Handed	Handle Material	Handle Orientation	Length of Cut	Overall Length
N5350	Straight	Standard	Stainless Steel	Sharp	Right	Metal	Bent	3"	9 1/2"

Utility Shears

- Stainless steel blades with sharp points.
- Soft to the touch handles.
- Extra Deep serrations are great for stem cutting.
- Cat. No. 544 models excellent for cutting, upholstery, headliners, rubber, and floral stems.
- Cat. No. 544KV is a Utility Kevlar® Shear for detail cutting applications. 544KV has a Rockwell 62C making it ideal for cutting Kevlar®.
- Cat. No. 545 used for cutting fabric, furniture making, and sewing.
- Cat No. 545-5 deep serrations are great for stem cutting.

543



545-5



Cat. No.	Blade Curvature	Blade Edge	Blade Material	Blade Tip	Handed	Handle Material	Handle Orientation	Length of Cut	Overall Length
543	Straight	Deep Serration	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Straight	1 7/8"	6 1/2"
544	Straight	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Straight	1 3/4"	6 3/8"
544KV	Straight	Serrated	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Straight	1 3/4"	6 3/8"
544S-MT	Straight	Serrated	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Straight	1 5/8"	6 1/4"
545	Straight	Serrated	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Straight	2 1/4"	6 3/4"
545-5	Straight	Deep Serration	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Straight	2 1/4"	7"

Kevlar® is a registered trademark of E.I. du Pont de Nemours and Company.

4-5/8" Lightweight Threadclip

- Blades come apart quickly and easily with one screw construction.
- Plastic molded body.

704



Cat. No.	Blade Curvature	Blade Edge	Blade Material	Blade Tip	Handed	Handle Material	Handle Orientation	Length of Cut	Overall Length
704	Straight	Standard	Stainless Steel	Sharp	Right	Molded Plastic	Straight	1 1/2"	4 5/8"
704B	Straight	Standard	Stainless Steel	Blunt	Right	Molded Plastic	Straight	1 5/16"	4 3/4"

Stamped

5" Auto Return Snip


- Sharp points and curved blades make this the ideal tool for cutting flush to material and getting into tight spots.
- Spring return action.
- Great for embroidery work and thread cutting.



Cat. No.	Blade Curvature	Blade Edge	Blade Material	Blade Tip	Handed	Handle Material	Handle Orientation	Length of Cut	Overall Length
7305C	Curved	Standard	Stainless Steel	Sharp	Ambidextrous	Molded Plastic	Spring Loaded	1"	4 7/8"

8" By-Pass Pruner

- Precision ground stainless steel blades insure crisp, clean cuts every time!
- Spring return action helps guard against fatigue, and locking latch allows for safe storage and transport.
- This will be the best By Pass Pruner you will ever own!
- Excellent for trimming & shaping branches, willow stems, and evergreens.
- Great for poultry disjoints.



Cat. No.	Blade Curvature	Blade Edge	Blade Material	Blade Tip	Handed	Handle Material	Handle Orientation	Length of Cut	Overall Length
8BP	Straight	Standard	Stainless Steel	Sharp	Right	Molded Plastic	Spring Loaded	1 1/2"	8"