



## R-168

Versatile impact and cut protection with the ultimate grip.



Impact

Abrasion Protection

Chemical Protection



Cut



Medium Duty

## Medium duty gloves combining impact protection and high cut resistance with a secure cuff and PVC palm for maximum grip.

The Ringers 168 Super Hero Medium Duty Impact glove's versatility allows endless application options, balancing excellent protection against impact hazards and cuts with enhanced grip due to a PVC palm and seamless index finger design.

- Developed with Ringers' F3 Technology™ and patented TPR design for superior dexterity and comfort.
- PVC palm material with Kevlar® stitching and an added palm layer for enhanced cut resistance.
- A hook and loop pull tab closure and high visibility provides added security on the job.



### Industries

- Food Processing
- Manufacturing
- Mining
- Oil and gas
- Machinery and Equipment
- Automotive Aftermarket

### Applications

- Makeup and breakout tools
- Running tools into the wellbore
- Handling explosives
- Assembly and disassembly of large pipes
- Engagement and release of drill string slips
- Unloading and stacking pipe
- Preparation of site - unloading of lines and valves
- Set-up of pressure manifold and tubing injector head
- Preparation of site - set-up and disassembly of tool string
- General pumping work
- Handling iron - rigging work
- Handling of tools
- Heavy machine operation
- Equipment repair & maintenance
- Maintenance of plant and machines
- Unpacking of bulk goods
- Scaffolding
- Loading and hauling
- Assembling and mounting components
- Seizing rough blocs and cylinders
- Production line support & maintenance



# R-168

Versatile impact and cut protection with the ultimate grip.

## Key Features

- Improved TPR design for greater impact protection, rated ANSI/ISEA 138 Level 2
- PVC palm material with Kevlar® stitching for maximum grip
- Additional palm layer for enhanced cut resistance
- Secure cuff with hook and loop TPR pull tab closure
- Wrap around index finger protecting wear and tear zone
- High visibility for increased safety

## Performance Standards & Regulatory Compliance

REACH Compliant



3X43EP



ABR



CUT

## Specifications

| BRAND   STYLE | DESCRIPTION                                     | Gauge | SIZE                 | COLOR         | PACKAGE                       |
|---------------|-------------------------------------------------|-------|----------------------|---------------|-------------------------------|
| RINGERS R168  | Liner Material: HPPE<br>Cuff Style: Safety Cuff |       | 8, 9, 10, 11, 12, 13 | Yellow Hi Viz | • 5 pairs/bag, 10 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:  
[www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

