



KLEENGUARD* A20 Breathable Particle Protection Coveralls

Product Information

Zipper Front	White Code	Blue Denim Code	Size	Quantity
	35671*	--	S	24
	49002	58532	M	24
	49003	58533	L	24
	49004	58534	XL	24
	49005	58535	2XL	24
	49006	58536	3XL	20
	49007	58537	4XL	20
	35670*	--	5XL/6XL	20

Zipper Front, Elastic Wrists & Ankles	White Code	Blue Denim Code	Size	Quantity
	35810*	--	S	24
	49102	58502	M	24
	49103	58503	L	24
	49104	58504	XL	24
	49105	58505	2XL	24
	49106	58506	3XL	20
	49107	58507	4XL	20
	30920*	23998	5XL	20
	35669*	--	5XL/6XL	20

Zipper Front, Elastic Wrist, Ankles & Hood	White Code	Blue Denim Code	Size	Quantity
	49112	58512	M	24
	49113	58513	L	24
	49114	58514	XL	24
	49115	58515	2XL	24
	49116	58516	3XL	20
	49117	58517	4XL	20
	30924*	30953	5XL	20


Zipper Front, Elastic Wrists, Ankles, Hood & Boots	White Code	Blue Denim Code	Size	Quantity
	49122	58522	M	24
	49123	58523	L	24
	49124	58524	XL	24
	49125	58525	2XL	24
	49126	58526	3XL	20
	49127	58527	4XL	20
	27258*	30910	5XL	20

Fabric Properties

Physical Properties	Results	Test Method
Tensile Strength – MD	26.4 lbs	ASTM D 5034
Tensile Strength – CD	17.2	ASTM D 5034
Trapezoidal Tear - MD	4.8 lbs	INDA IST 100.2
Trapezoidal Tear – CD	9.2 lbs	INDA IST 100.2
Elongation – MD	56.7%	ASTM D 5034
Elongation – CD	45%	ASTM D 5034
Mullen Burst	36.4 psi	ISO 13938-1
Static Decay (<0.5sec)	Pass	NFPA99
Flammability	Class 1	CPSC 1610
Barrier Properties	Results	Test Method
Hydrohead	72.8 cm	ASTM D 737
Comfort Properties	Results	Test Method
Air Permeability	41.8 cfm	ASTM D 737
Moisture Vapor Transport	4639 g/m ² /24hr	ASTM E96

Additional Attributes

Breathable, MICROFORCE* Barrier SMS Fabric
 Non-latex polyisoprene elastic
 No silicone
 No BHT preservative
 REFLEX* Design – see catalog for sizing chart
 Seamless front
 Zipper flap
 NFPA 99 Compliant Antistatic material



*Made-to-Order Codes

Workmanship Requirements

Coveralls shall be made in accordance with reasonable industry practice with respect to holes, tears, wrinkles, cleanliness, and foreign materials or dirt. For additional information: 1-888-346-4652 or kimtech@kcc.com

Kimberly-Clark warrants that its products (1) comply with K-C's standard specifications as of the delivery date to K-C's authorized distributors/direct purchasers and are warranted for the following periods from end user's date of purchase (verified by valid sales receipt) (a) five years for Balder Technology auto darkening filters; (b) two years for all other auto darkening filters; and (c) one year for powered air purifying respirators; (2) comply with all K-C labeling representations; and (3) are manufactured in compliance with all applicable federal, state, and local laws in effect at the time and place of manufacture of the products. THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. K-C is not liable for any kind of special, incidental, or consequential damages. K-C's liability for breach of contract, tort or other cause of action shall not exceed the product purchase price. Purchasers and users are deemed to have accepted the above warranty and limitation of liability, and cannot change the terms by verbal agreement or by any writing not signed by K-C. To the extent required by applicable law, K-C does not limit its liability for death/injury resulting from K-C's negligence.



Exceptional Workplaces®