

The Zyklop Ratchets, 3/8"



EAN:	4013288121165	Size:	285x240x55 mm
Part number:	05003596001	Weight:	3149 g
Article number:	8100 SB 4	Country of origin:	CZ
		Customs tariff number:	82041100

- Combines five different types of a ratchet in one
- Flywheel design and easy-to-grip free-turning sleeve for very high working speeds
- 38-piece set in a robust metal case
- Freely pivoting ratchet head
- With Take it easy tool finder: colour coding by size

38-piece Zyklop set in robust metal case: Zyklop ratchet with 3/8" drive. The 72 fine-pitched teeth enable a low return angle of only 5°. The ratchet head pivots freely and can be locked into any position by using the slide switch that is positioned on either side. It is even possible to work conveniently in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking positions at 0°, 15° und 90°, both to the right and left, ensure safe working without any slipping of the ratchet head. The ratchet can be used as a conventional screwdriver in the 0° position by attaching an adaptor and a bit. The flywheel design ensures rapid screwdriving. The rotation-symmetric construction of the Kraftform handle and the free-turning sleeve support rapid twisting. The outstanding design of the Kraftform handle fits perfectly into the hand preventing hand injuries such as blisters and calluses. The hard materials used for the handle ensure quick and easy hand repositioning without any danger of the skin "sticking" to the handle. The softer anti-slip zones enable the low-loss transfer of high torque. For 3/8" square sockets as well as 3/8" adaptors with square drive, equipped with ball lock. Including 12 imperial Zyklop sockets, 2 Zyklop extensions with free-turning sleeve, 1 T-handle, 1 wobble extension, 1 universal joint, 1 adaptor with quick-release chuck, 19 bits. "Take it easy" Tool Finder with colour coding according to sizes.

Web link

https://products.wera.de/en/zyklop_ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_3_8_the_zyklop_speed_ratchet_3_8_8100_sb_4.html

Wera - 8100 SB 4
05003596001 - 4013288121165

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

8100 SB 4 Zyklop Speed Ratchet Set, 3/8" drive, imperial, 38pieces



The Zyklop Ratchets, 3/8"

Set contents:



8000 B
05003550001 1 x 3/8" x 199 mm




8790 HMB
05003569001 1 x 1/4" x 29 mm
05003570001 1 x 5/16" x 29 mm
05003571001 1 x 11/32" x 29 mm
05003572001 1 x 3/8" x 29 mm
05003573001 1 x 7/16" x 29 mm
05003574001 1 x 1/2" x 29 mm
05003575001 1 x 9/16" x 29 mm
05003576001 1 x 5/8" x 30 mm
05003577001 1 x 11/16" x 30 mm
05003578001 1 x 3/4" x 30 mm
05003579001 1 x 13/16" x 30 mm
05003580001 1 x 7/8" x 30 mm



8789 B
05003581001 1 x 3/8" x 165 mm



8794 B
05003584001 1 x 3/8" x 76 mm



8795 B
05003585001 1 x 3/8" x 50 mm



8784 B1
05003590001 1 x 1/4" x 3/8" x 44 mm



8796 SB
05003591001 1 x 3/8" x 125 mm



8796 LB
05003592001 1 x 3/8" x 200 mm



851/1 Z PH
05072072001 1 x PH 2 x 25 mm
05072074001 1 x PH 3 x 25 mm



855/1 Z PZ
05072082001 1 x PZ 2 x 25 mm
05072084001 1 x PZ 3 x 25 mm



867/1 Z TORX® BO
05066500001 1 x TX 10 x 25 mm
05066505001 1 x TX 15 x 25 mm
05066510001 1 x TX 20 x 25 mm
05066515001 1 x TX 25 x 25 mm
05066520001 1 x TX 27 x 25 mm
05066525001 1 x TX 30 x 25 mm
05066530001 1 x TX 40 x 25 mm



800/1 Z
05072059001 1 x 1 x 5.5 x 25 mm



840/1 Z Hex-Plus
05135069001 1 x 9/64" x 25 mm
05135071001 1 x 5/64" x 25 mm
05135072001 1 x 3/32" x 25 mm
05135073001 1 x 1/8" x 25 mm
05135074001 1 x 5/32" x 25 mm
05135075001 1 x 3/16" x 25 mm
05135079001 1 x 7/32" x 25 mm

Web link

https://products.wera.de/en/zyklop_ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_3_8_the_zyklop_speed_ratchet_3_8_8100_sb_4.html

Wera - 8100 SB 4
05003596001 - 4013288121165

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

The Zyklop Ratchets, 3/8"

Zyklop "6 in 1"



1. Fine-tooth ratchet 2. Flex-head ratchet 3. Angle ratchet 4. Quick-release ratchet 5. Power ratchet 6. Screwdriver

Pivots freely



The ratchet head pivots freely and can be locked into any defined position by using the slide switch that is positioned on either side. It is even possible to work in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking at 0°, 15° and 90°, both to the right and left, ensure safe working without any slipping of the ratchet head.

Fast movers




The Zyklop Speed ratchets are really fast movers. The gyrating mass design means that screwdriving is accelerated. The rotation-symmetric structure of the Kraftform handle and the free-turning sleeve reinforce this rapid twisting process, particularly when the ratchet does not engage due to too little resistance in the thread.

Simple direction change



All Zyklop Speed ratchets feature a thumbwheel that can be used to quickly and easily switch between clockwise and anticlockwise rotation, at any position. No complicated handling, no loss of time!

Low return angle




The reversible ratchet with 72 fine-pitched teeth has a low return angle of only 5°. This short stroke allows fast and precise work in all types of installation.

Screwdriver



The ratchet can be used as a conventional screwdriver in the 0° position by attaching a bitholding adaptor and a bit.

Ball lock



The ball lock holds the sockets and attachments securely, ensuring safe working. A changeover into any predefined position is completed by simply pressing the release button – this is even the case in the 90° position.

Two-tone foam insert



Perfectly conceived in every detail: the storage case for the Zyklop Speed ratchet sets! The two-tone foam insert section means that the tools can be quickly and reliably replaced, and that missing tools can be detected immediately. The tools and their position can be clearly seen in the lid where they have been laser-etched, ensuring that they are legible even when the insert section is covered with grease, dirt or oil. Additionally, the foam section can be removed and placed in the drawer of a tool cabinet or trolley.

Web link

https://products.wera.de/en/zyklop_ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_3_8_the_zyklop_speed_ratchet_3_8_8100_sb_4.html

Wera - 8100 SB 4
05003596001 - 4013288121165

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

8100 SB 4 Zyklop Speed Ratchet Set, 3/8" drive, imperial, 38pieces

The Zyklop Ratchets, 3/8"



Web link

https://products.wera.de/en/zyklop_ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_3_8_the_zyklop_speed_ratchet_3_8_8100_sb_4.html

Wera - 8100 SB 4
05003596001 - 4013288121165

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de