

## 15 and 20 Amp Receptacles

### Style Line® Decorator Receptacles

- High-impact nylon face resists breaking, chipping and cracking.
- Will accept locking fork terminal to comply with ABYC standards.
- Available in 4 colors for any decor with matching wall plates.
- Smooth, high-gloss finish for rich appearance.

### Commercial Style Line® Decorator Series



Description	Color	Standard Duplex	Duplex, Tamper-Resistant	Duplex, Weather and Tamper-Resistant
15A 125V duplex receptacle.	Black	<b>DR15BLK</b>	<b>DR15BLKTR</b>	<b>DR15BLKWTRTR</b>
	Brown	<b>DR15</b>	<b>DR15TR</b>	<b>DR15WRTR</b>
	Gray	<b>DR15GRY</b>	<b>DR15GRYTR</b>	<b>DR15GRYWTRTR</b>
	Ivory	<b>DR15I</b>	<b>DR15ITR</b>	<b>DR15IWTRTR</b>
	Light Almond	<b>DR15LA</b>	<b>DR15LATR</b>	<b>DR15LAWTRTR</b>
	White	<b>DR15WHI</b>	<b>DR15WHITR</b>	<b>DR15WHIWTRTR</b>



DR15TR



DR15GRYWTRTR

### Commercial Series



Description	Color	Standard Duplex, Spec. Grade, Side Wired	Duplex, Tamper-Resistant	Duplex, Weather and Tamper-Resistant, Back and Side Wired
15A 125V duplex receptacle.	Black	<b>CR15BLK</b>	<b>CR15BLKTR</b>	<b>BR15BLKWTRTR</b>
	Brown	<b>CR15</b>	<b>CR15TR</b>	<b>BR15WRTR</b>
	Gray	<b>CR15GRY</b>	<b>CR15GRYTR</b>	<b>BR15GRYWTRTR</b>
	Ivory	<b>CR15I</b>	<b>CR15ITR</b>	<b>BR15IWTRTR</b>
	Light Almond	<b>CR15LA</b>	<b>CR15LATR</b>	<b>BR15LAWTRTR</b>
	White	<b>CR15WHI</b>	<b>CR15WHITR</b>	<b>BR15WHIWTRTR</b>



CR15TR



BR15IWTRTR

Note: All devices above will accept locking fork terminal to comply with ABYC standards. See page Tech-10 for Tamper and Weather Resistant descriptions.

### Extra Heavy Duty Single Receptacles

Description	Color	Catalog Number
15A 125V single receptacle.	Brown	<b>HBL5251</b>
	Ivory	<b>HBL5251I</b>
20A 125V single receptacle.	Brown	<b>HBL5361</b>
	Ivory	<b>HBL5361I</b>



HBL5251



HBL5361I

### Corrosion-Resistant Receptacles



Description	Color	Catalog Number
15A 125V yellow corrosion-resistant duplex receptacle. Use where salt or other corrosive elements are a problem.	Yellow	<b>HBL52CM62</b>
Same as HBL52CM62 except ivory in color.	Ivory	<b>HBL52CM62I</b>



HBL52CM62I



HBL8200ILI

### Special Application Illuminated Receptacle

Description	Color	Catalog Number
Illuminated receptacle 15A 125V grounding. A high quality receptacle with an illuminated face. Ideal for use in halls or as a gentle night light.	Ivory	<b>HBL8200ILI</b>

Note: See page Tech-10 for Weather Resistant description.