



## KLEENGUARD\* A65 Flame Resistant Coveralls & Lab Coats


### Product Information

Zipper Front	Code	Size	Qty
	45312	M	25
	45313	L	25
	45314	XL	25
	45315	2XL	25
	45316	3XL	25
	45317	4XL	21
	32420	5XL	21
	32417	6XL	21


### Zipper Front, Elastic Wrists, Ankles & Hood

Code	Size	Qty	
	45322	M	25
	45323	L	25
	45324	XL	25
	45325	2XL	25
	45326	3XL	21
	45327	4XL	21
	23558*	5XL	21
	23559*	6XL	21

### Zipper Front, Elastic Wrist, Ankles, Hood & Boots

Code	Size	Qty	
	45352	M	25
	45353	L	25
	45354	XL	25
	45355	2XL	25
	45356	3XL	21
	45357	4XL	21
	30952*	5XL	21
	30951*	6XL	21

### Lab Coat with Hook & Loop Closure, No Pocket

Code	Size	Qty	
	12810	M	25
	12811	L	25
	12812	XL	25
	12813	2XL	25
	12814	3XL	25
	12815	4XL	25
	12886*	5XL	25
	12887*	6XL	25

\*Made-to-Order Codes

### Workmanship Requirements

Apparel shall be made in accordance with reasonable industry practice with respect to holes, tears, wrinkles, cleanliness, and foreign materials or dirt.

For Additional information: Contact your Kimberly-Clark representative, our Customer Service Team (888)-346-GOKC (4652) or [KCPInfo@kcc.com](mailto:KCPInfo@kcc.com)

Rev. 9/2017

### Fabric Properties

Physical Properties	Test Methods	Target
Tensile Strength (MD)	ASTM D5034	19.1 lbs.
Tensile Strength (CD)	ASTM D5034	14.1 lbs.
Trapezoidal Tear (MD)	ASTM D5733	5.4 lbs.
Trapezoidal Tear (CD)	ASTM D5733	8.5 lbs
Flammability	NFPA 701 Can/CGSB-155. 20-2000	Pass Compliant
Static Decay (<0.5 sec)	NFPA 99	Pass
Mullen Burst	ASTM E96-80	30 psi

Comfort Properties	Test Methods	Target
Air Permeability	ASTM D737	57.9 cfm
WTVR	ASTM E96	5000 g/m <sup>2</sup> /24 hrs

### Additional Attributes

FR treated cellulosic and polyester spunlace material, Blue
Non-latex polyisoprene elastic
Product not made with silicone
Not made with natural rubber latex
Not made with BHT preservative
Flame resistant compliant per NFPA 701 FLAME PROPAGATION TEST (1999 edition)
Complies with the flame resistance requirements cited by paragraph 6.1 of CAN/COSB-155.20-2000
Meets ANSI/ISEA 101-1996 sizing standards
Serged Seams

Do not use for fire protection. Avoid open flame or intense heat. KLEENGUARD\* A65 garments do not provide thermal insulation/protection.

Kimberly-Clark warrants that its products (1) comply with K-C's standard specifications as of the delivery date to K-C's authorized distributors/direct purchasers and are warranted for the following periods from end user's date of purchase (verified by valid sales receipt) (a) five years for Balder Technology auto darkening filters; (b) two years for all other auto darkening filters; and (c) one year for powered air purifying respirators; (2) comply with all K-C labeling representations; and (3) are manufactured in compliance with all applicable federal, state, and local laws in effect at the time and place of manufacture of the products. **THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** K-C is not liable for any kind of special, incidental, or consequential damages. K-C's liability for breach of contract, tort or other cause of action shall not exceed the product purchase price. Purchasers and users are deemed to have accepted the above warranty and limitation of liability, and cannot change the terms by verbal agreement or by any writing not signed by K-C. To the extent required by applicable law, K-C does not limit its liability for death/injury resulting from K-C's negligence.



Public