

PIG® Rip-&-Fit® HazMat Mat Roll in Dispenser Box

#MAT342 - Heavy-weight • 15" x 60'



Extra perforations let you create custom sizes of PIG HazMat Mat without cutting. Just "rip" it along the easy-tear perfs and "fit" it into place.

- Absorbs the widest range of acids, bases, corrosives, chemicals and unknown liquids - even those with high concentrations like 98% sulfuric acid and 30% sodium hydroxide
- Lasts 2x longer than ordinary mats for fewer change-outs
- Chemical-resistant mat won't degrade or cause a dangerous reaction upon contact with corrosive spills
- No matter how you rip it, this mat features the proven eight-layer, 100% polypropylene construction of PIG Mat, the strongest mat on the market!
- Exclusive dimple pattern speeds wicking of liquid throughout mat for faster, easier cleanup
- Highly-absorbent, fine-fiber construction won't leave behind liquids or fiber residue
- Pink color is easily distinguishable to assure workers use the correct mat during a spill emergency
- Perforated every 3-3/4" across width and every 10" across length; "rip" the perfect sized Mat, then "fit" it into place
- Dispenser box makes mat easy to access, carry and store while protecting contents from dirt and moisture
- Heavy-weight construction is highly durable and absorbent for demanding tasks and large-volume cleanups

Always in stock. Ships within 24 hours.



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT342 - Pg 1 of 2

MAT342 Specifications

Color:	Pink
Dimensions:	15" W x 60' L
Mat Weight:	Heavy-weight
Fluids Absorbed:	Acids, Bases & Unknowns
Absorbency:	Up to 7.9 gal. per box
Absorbency per:	Up to 7.9 gal. per roll
Dispenser:	Yes
Perforated:	Every 10" Lengthwise & Every 3.75" Widthwise
Poly-Backing:	No
UV Resistant:	No
Sold as:	1 roll per box
Weight:	8 lbs.
# per Pallet:	54
Composition:	100% polypropylene
UNSPSC:	47131901

Technical Information

Warnings & Restrictions:

HAZ-MAT Notice

To ensure effectiveness and your safety, we recommend that you conduct compatibility and absorption testing of your chemicals with PIG® HAZ-MAT products prior to purchase. If you have any questions or need samples to test, please call Technical Services.

Technical Documents:

(Available at newpig.com)

Product Data Sheet (PDS)

Safety Data Sheet (SDS)

Chemical Compatibility (CCG)



MAT342 Metric Equivalent

Dimensions:	38.1cm W x 18m L
Absorbency:	Up to 29.9 L per box
Absorbency per:	Up to 29.9 L per roll
Weight:	3.6 kg



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT342 - Pg 2 of 2