


# 115 Standard Duty Loop Hanger

## Features

- Flared edges help prevent any sharp surfaces from coming into contact with the pipe (1/2" to 4" sizes)
- Retained insert nut helps ensure the loop hanger and insert nut stay together
- Recommended for the suspension of stationary non-insulated pipe lines
- Manufactured to use the minimum rod size permitted by NFPA® for fire sprinkler piping
- Conforms with Federal Specification WW-H-171 (Type 10), Manufacturers Standardization Society (MSS) SP-58 and SP-69 (Type 10)

The 115 Standard Duty Loop Hanger, part of the CADDY® line of fasteners and supports from ERICO, is ideal for suspending stationary, non-insulated pipe lines, including CPVC pipes, in fire sprinkler systems. A knurled insert nut helps simplify vertical adjustments and flared edges on the base (1/2" to 4" sizes) help protect pipes from coming into contact with any sharp edges of the hanger.



Material: Steel  
Finish: Pre-galvanized



Part Number	Pipe Size	Outer Diameter OD	Rod Size RS	A	B	C	Static Load F
1150050EG	1/2"	0.840"	3/8"	2 13/16"	1 1/8"	1"	300 lb
1150075EG	3/4"	1.050"	3/8"	3"	1 3/16"	15/16"	300 lb
1150100EG	1"	1.315"	3/8"	3 1/4"	1 3/8"	15/16"	300 lb
1150125EG	1 1/4"	1.660"	3/8"	3 9/16"	1 1/2"	15/16"	300 lb
1150150EG	1 1/2"	1.900"	3/8"	3 13/16"	1 5/8"	15/16"	300 lb
1150200EG	2"	2 3/8"	3/8"	4 1/4"	1 7/8"	15/16"	300 lb
1150250EG	2 1/2"	2 7/8"	3/8"	5 9/16"	2 13/16"	1 9/16"	525 lb
1150300EG	3"	3 1/2"	3/8"	6 9/16"	3 1/2"	1 15/16"	525 lb
1150350EG	3 1/2"	4"	3/8"	7 1/16"	3 3/4"	1 15/16"	585 lb
1150400EG	4"	4 1/2"	3/8"	7 9/16"	4"	1 15/16"	650 lb
1150500EG	5"	5 9/16"	1/2"	9 13/16"	4 3/4"	2 1/4"	1,000 lb
1150600EG	6"	6 5/8"	1/2"	11 5/16"	6 5/16"	3 5/16"	1,000 lb
1150800EG	8"	8 5/8"	1/2"	12 7/8"	6 7/8"	2 7/8"	1,000 lb

## Surge Restraint

### Features

- Surge restraint for 115 standard duty loop hangers

### Specifications

Material: Steel  
Finish: CADDY® ARMOUR



Part Number	Pipe Size
SR6	1/2" - 2"



cULus is a registered certification mark of UL LLC. FM is a registered certification mark of FM Approvals LLC, LTD. NFPA is a registered trademark of National Fire Protection Association, Inc.

#### WARNING

ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at [www.erico.com](http://www.erico.com) and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

Copyright © 2013 ERICO International Corporation. All rights reserved. CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

