

PIG® Oil-Only Absorbent Mat Roll

#MAT401 - Heavy-weight • 30" x 150'



Lasts 2x longer than ordinary mats for fewer change-outs, while only absorbing oil and fuels, NOT water. Loves oil. Hates water.

- Our most cost-effective mat when you only need to absorb oil-based liquids
- Eight layers of 100% polypropylene are thermally bonded to make PIG Mat the strongest mat on the market; won't rip, tear or fray even when saturated
- Exclusive dimple pattern speeds wicking of liquid throughout mat for faster, easier cleanup
- Highly absorbent, fine-fiber construction won't leave behind liquids or fiber residue
- Absorbs oil and fuels, NOT water
- White color tells you it's only for oils and fuels; draws attention to machine leaks and clearly shows saturation level during spill response
- Floats to clean up spills on water
- Can be wrung out and incinerated after use to reduce waste or for fuels blending
- Flame-resistant material won't burn immediately like cellulose mats; melts when exposed to high heat while on the job
- Rolls are ideal for covering large areas and soaking up leaks and overspray
- Easy-tear perforations let you take only what you need, so you use less mat and save money
- Heavy-weight construction is highly durable and absorbent for demanding tasks and large-volume cleanups

Always in stock. Ships within 24 hours.



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT401 - Pg 1 of 2

MAT401 Specifications

| | |
|-------------------------|---|
| Color: | White |
| Dimensions: | 30" W x 150' L |
| Mat Weight: | Heavy-weight |
| Fluids Absorbed: | Oil-based Liquids But Not Water |
| Absorbency: | Up to 40.2 gal. per bag |
| Absorbency per: | Up to 40.2 gal. per roll |
| Dispenser: | No |
| Perforated: | Every 10" Lengthwise & Centered Widthwise |
| Poly-Backing: | No |
| UV Resistant: | No |
| Sold as: | 1 roll per bag |
| Weight: | 30 lbs. |
| # per Pallet: | 12 |
| Composition: | 100% Polypropylene |
| UNSPSC: | 47131901 |

Technical Information

Warnings & Restrictions:

There are no known warnings and restrictions for this product.

Regulations and Compliance:

40 CFR 122.26 - When applying for a National Pollutant Discharge Elimination System (NPDES) permit, facilities must have a plan in place that describes actions, procedures, control techniques, management practices and equipment available to prevent illegal discharge of pollutants into waterways.

40 CFR 112.7 - SPCC planning requirements state that facilities subject to these regulations must have written plans in place discussing the products, countermeasures and procedures that are in place, or will be taken by the facility to prevent discharge of oil into waters of the United States.

Technical Documents:

(Available at newpig.com)

Product Data Sheet (PDS)

Safety Data Sheet (SDS)

MAT401 Metric Equivalent

| | |
|------------------------|------------------------|
| Dimensions: | 76.2cm W x 46m L |
| Absorbency: | Up to 152.2 L per bag |
| Absorbency per: | Up to 152.2 L per roll |
| Weight: | 13.6 kg |



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT401 - Pg 2 of 2