


PIG® STAT-MAT® Absorbent Pad

#MAT214 - Heavy-weight • 15" x 20" • 100 pads



The ONLY absorbent mat for fuels and solvents proven to dissipate static.

- The best mat you can buy to reduce the risk of electrostatic discharge; a critical precaution around flammable liquids and vapors
- STAT-MAT Pads and Rolls pass NFPA 99 standards for static decay and surface resistivity, making them perfect for fueling areas and solvent cleanup
- Absorbs and retains oils and fuels - including acetone, benzene, gasoline, toluene, xylene, mineral spirits and jet fuels - but not water
- Lasts 2x longer than ordinary mats for fewer change-outs; Eight layers of 100% polypropylene are thermally bonded to make PIG Mat the strongest mat on the market; won't rip, tear or fray even when saturated
- Exclusive dimple pattern speeds wicking of liquid throughout mat for faster, easier cleanup
- Highly absorbent, fine-fiber construction won't leave behind liquids or fiber residue
- Packaged in special static-dissipative bags to help reduce static charge buildup
- Floats to clean up spills on water
- Flame-resistant material won't burn immediately like cellulose mats; melts when exposed to high heat while on the job
- White color tells you it's only for oils and fuels
- Pads are ideal for catching drips and soaking up spills
- Easy-tear perforations let you take only what you need, so you use less mat and save money
- Heavy-weight construction is highly durable and absorbent for demanding tasks and large-volume cleanups

Always in stock. Ships within 24 hours.



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT214 - Pg 1 of 2

MAT214 Specifications

Color:	White
Dimensions:	15" W x 20" L
Mat Weight:	Heavy-weight
Fluids Absorbed:	Oil-based Liquids But Not Water
Absorbency:	Up to 22 gal. per bag
Absorbency per:	Up to 28.16 oz. per pad
Dispenser:	No
Perforated:	Centered Widthwise
Poly-Backing:	No
UV Resistant:	No
Sold as:	100 pads per bag
Weight:	17 lbs.
National Stock Number (NSN):	4235-01-308-5150
# per Pallet:	30
Composition:	100% polypropylene
UNSPSC:	47131901

MAT214 Metric Equivalent

Dimensions:	38.1cm W x 50.8cm L
Absorbency:	Up to 83.3 L per bag
Absorbency per:	Up to 832.7 mL per pad
Weight:	7.7 kg

Technical Information

Warnings & Restrictions:

There are no known warnings and restrictions for this product.

Certifications, Approvals and Ratings:

NFPA 99
NFPA 77

Regulations and Compliance:

29 CFR 1910.106(h)(7)(i)(a) - When working with or around flammable liquids, precautions must be taken to prevent static and other sources of ignition that could ignite flammable vapors.

40 CFR 122.26 - When applying for a National Pollutant Discharge Elimination System (NPDES) permit, facilities must have a plan in place that describes actions, procedures, control techniques, management practices and equipment available to prevent illegal discharge of pollutants into waterways.

40 CFR 112.7 - SPCC planning requirements state that facilities subject to these regulations must have written plans in place discussing the products, countermeasures and procedures that are in place, or will be taken by the facility to prevent discharge of oil into waters of the United States.

Technical Documents:

(Available at newpig.com)

Product Data Sheet (PDS)

Safety Data Sheet (SDS)



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT214 - Pg 2 of 2