

HAND CARRIED & ECONO™ SPILL PAK KITS

Perfect for stashing behind the seat of a truck, in a cabinet or placing in tool box, the Hand Carried and Econo Spill Pak Kits are ideal for spill response on the go! Providing quick and efficient clean-up for your unplanned spills, they can be refilled, but are so economical, we feel they're disposable!



HAND CARRIED & ECONO™ SPILL PAK KITS

Part #	Description	Absorbs up to gal. (L)	Weight lb. (kg)	Kit Includes
ENP D715 Universal	Hand Carried	6 (23)	6 (2.7)	1 Spill Pak Bag, 15 Pads, 2 Medium Socks, 1 Pair Nitrile gloves, 2 Disposal Bags, 1 Instruction Sheet, 1 MSDS(s).
ENP D717 Aggressive	Hand Carried			
ENP D716 Oil Only	Hand Carried			
13-SP2U Universal	Econo	5 (19)	5 (2.3)	1 Spill Pak Bag, 12 Pads, 3 Medium Socks, 1 Pair Nitrile Gloves, 1 Disposal Bag with tie, 1 Instruction Sheet, 1 MSDS(s).
13-SP2A Aggressive	Econo			
13-SP2O Oil Only	Econo			

Regulations: 40 CFR 112.7, 40 CFR 122.26, 40 CFR 263.30, 40 CFR 263.31, EPA, SPCC and NPDES

CHEMKLENZ® NEUTRALIZING SPILL KITS

Nasty spill? You can never be too safe when dealing with unknown chemicals and liquids. Be armed with ENPAC's newest Chemkrenz® Neutralizing Kits! Fully ready to tackle your meanest of spills, Chemkrenz® Nano technology makes it the market's leading Absorbent and Neutralizer for acids, bases, caustics, solvents and more. Three sizes available.



X1



X5



X10



NEUTRALIZES ACIDS & BASES

CHEMKLENZ NEUTRALIZING SPILL KITS

Part #	Description	Absorbs up to gal. (L)	Weight lb. (kg)	Kit Includes
13-NNX1-A	Chemkrenz® Neutralizing X1	.3 (1)	3 (1.4)	1 - 500 gm ChemKrenz® Granule Bag, 1 pair Goggles, 1 Disposal Bag with tie, 1 pair Nitrile Gloves, 1 Dust Pan with Brush, 1 Clear zipper bag.
13-NNX5-A	Chemkrenz® Neutralizing X5	5 (10)	5.2 (2.4)	2 - 500 gm ChemKrenz® Granule Bags, 1 pair Goggles, 2 Disposal Bags with Ties, 1 pair Nitrile Gloves, 1 Dust Pan with Brush, 1 Fast Pack Bag, 5 Pads, 2 Med. socks, 1 Red Demand Seal.
13-NNX10-A	Chemkrenz® Neutralizing X10	10 (37.9)	13 (5.9)	2 - 750 gm ChemKrenz® Granule Shakers, 1 pair Goggles, 4 Disposal Bags with Ties, 1 pair Nitrile Gloves, 1 Dust Pan with Brush, 1 Speed Duffel Bag, 20 Pads, 3 Med. socks, 2 Large socks, 1 Red Demand Seal.

Regulations: 40 CFR 112.7, 40 CFR 122.26, 40 CFR 263.30, 40 CFR 263.31, EPA, SPCC and NPDES

DELUXE LONG HAUL TRUCK SPILL KIT

The Deluxe Long Haul Truck Spill Kit can be used as a truck-mounted container under semi-trucks/trailers, or as a spill response unit in almost any location when mounted to the wall. Attaches easily to trailer undercarriage or walls utilizing molded or slotted holes for multiple mounting options. Contents are safely contained in the lockable ENPAC® Poly-Edge™ which has a durable weather and water resistant gasket seal that keeps all stored items secure and dry. This Deluxe Kit also includes an ENPAC® 100 gallon Prowler™ Pop-Up Pool – for immediate spill containment to the widest range of chemicals – and a complete Leak Repair Kit.



ECONO LONG HAUL TRUCK SPILL KIT

A Spill Kit as mobile as you are! Your quick and convenient travel pal for any spill while you're on the move! Keep it handy in your cab or small enough to store in a toolbox. Includes many of the same items featured in the Long Haul Truck Deluxe.



LONG HAUL SPILL KITS

Part #	Description	Spill Cap. gal. (L)	Absorbs up to gal. (L)	Weight lb. (kg)	Kit Includes
13-TWSK-U Universal	Long Haul Truck	110 (416)	10 (38)	27 (12.2)	1 Poly-Edge™ Mountable (lockable) Storage Container, 1 Leak Repair Kit, 1 - 100 Gallon Prowler Pop-Up Pool, 25 Pads, 4 Socks, 1 - 1-Gal Jug ENSORB®, 2 Disposable Bags with Ties, 1 pair Nitrile Gloves, 1 pair Goggles, 1 Emergency Response Guide and Instruction Sheet.
13-TWSK-O Oil Only					
13-ELHT-U Universal	Econo Long Haul Truck	25 (95)	5 (19)	7 (3.2)	1 - 1Qt. Zip Bag ENSORB®, 1 - 20-Gallon Prowler Pop-Up Pool, 10 Pads, 4 Med. Socks, 1 pair Goggles, 1 pair Nitrile Gloves, 1 Disposal Bag with Tie, 1 Emergency Response Guide and instruction sheet.
13-ELHT-O Oil Only					

Regulations: 40 CFR 112.7, 40 CFR 122.26, 40 CFR 263.30, 40 CFR 263.31, EPA, SPCC and NPDES