

WOOSTER®



fabulous fourteen

ROLLER PROGRAM

They are the perfect in-between: more production than 9-inch or 12-inch covers, less weight and more control than 18-inch. Our expanded 14-inch roller program includes nine different fabrics, in a range of pile heights to paint very smooth to very rough surfaces. All of them have a green™ double-thick polypropylene core to maintain strength.



Pro/Doo-Z® FTP™ Double pinstripe no-shed fabric. HydroFlow™ technology offers controlled paint release. All paints (flat to gloss), enamels, primers, urethanes, epoxies.

Cat. No.	UPC 0-71497-	Size	Nap	Case Qty.	Cubic Ft. Per Case	Pounds Per Case
RR665	17737-7	14"	3/16"	6	.376	1.55
RR666	17696-7	14	3/8	6	.376	1.62
RR667	17697-4	14	1/2	6	.376	1.66



Pro/Doo-Z® Golden pinstripe shed-resistant fabric. Finest finish, resists matting. All paints (flat to gloss), enamels, primers, urethanes, epoxies.

Cat. No.	UPC 0-71497-	Size	Nap	Case Qty.	Cubic Ft. Per Case	Pounds Per Case
RR642	12315-2	14"	3/8"	6	.376	1.57
RR643	16794-1	14	1/2	6	.376	1.66



Super/Fab® FTP™ Lager-colored high capacity, shed-resistant fabric. HydroFlow technology offers controlled paint release. All flat, eggshell, satin paints.

Cat. No.	UPC 0-71497-	Size	Nap	Case Qty.	Cubic Ft. Per Case	Pounds Per Case
RR923	17727-8	14"	3/8"	6	.376	1.78
RR924	17728-5	14	1/2	6	.376	1.85
RR925	17729-2	14	3/4	6	.473	2.01



Super/Fab® Golden yellow, high production fabric. Complete coverage, smooth results. All flat to satin paints, stains, waterproofing.

Cat. No.	UPC 0-71497-	Size	Nap	Case Qty.	Cubic Ft. Per Case	Pounds Per Case
R239	17806-0	14"	3/8"	6	.376	1.80
R240	66028-2	14	1/2	6	.376	1.83
R241	66038-1	14	3/4	6	.473	2.01
R243	66058-9	14	1 1/4	6	1.023	2.73



50/50™ Shed-resistant knit fabric blend of 50% lambswool and 50% polyester. Wool provides maximum capacity; polyester resists matting. All flat, satin or semigloss paints, stains, waterproofing.

Cat. No.	UPC	Size	Nap	Case Qty.	Cubic Ft. Per Case	Pounds Per Case
R295	16795-8	14"	1/2"	6	.376	1.68
R296	16796-5	14	3/4	6	.473	1.87
R298	16797-2	14	1 1/4	6	1.023	2.71



Cirrus™ High-capacity white polyamide yarn fabric with a green stripe. Low spatter and durable, excellent for rough surfaces. All flat paints, stains, sizings.

Cat. No.	UPC	Size	Nap	Case Qty.	Cubic Ft. Per Case	Pounds Per Case
R193	17750-6	14"	3/8"	6	.376	1.50
R194	17751-3	14	1/2	6	.376	1.80
R195	17752-0	14	3/4	6	.473	1.92
R196	17753-7	14	1	6	1.023	2.50



Micro Plush™ Microfiber fabric delivers a very uniform, even finish. Great for multiple coats in deep tone colors. All paints and enamels.

Cat. No.	UPC	Size	Nap	Case Qty.	Cubic Ft. Per Case	Pounds Per Case
R235	16799-6	14"	5/16"	6	.376	1.79



Mohair Blend™ Shed-resistant for all paints, enamels, urethanes, epoxies, floor toppings. Naturally smooth painting qualities of mohair, blended with added resiliency of polyester for better production.

Cat. No.	UPC	Size	Nap	Case Qty.	Cubic Ft. Per Case	Pounds Per Case
R207	16800-9	14"	1/4"	6	.376	1.71



Super Doo-Z® Favorite of professionals and DIY painters, for its price and its performance. Shed-resistant fabric reduces dripping for neat results with all paints, enamels, varnishes.

Cat. No.	UPC	Size	Nap	Case Qty.	Cubic Ft. Per Case	Pounds Per Case
R205	16819-1	14"	3/8"	6	.376	1.60

Sherlock® 14" Frame Durable, green™ fiberglass-reinforced nylon cage and endcaps. Smooth-rolling bearings eliminate graying and shank wear. Quick-release spring prevents roller slippage, yet allows hands-free removal. Comfortable polypropylene grip with reinforced threads, Sherlock GT® pole compatible.



Cat. No.	UPC	Size	Overall Length	Case Qty.	Cubic Ft. Per Case	Pounds Per Case
R017	16779-8	14"	15"	6	.802	7.07



Header Sign

(24" long x 10" high) helps you sell these productive rollers! Request #32518.

