

Great Satellite Jumbo-Koter® Items



RR393-4½"
Jumbo-Koter Pro/Doo-Z® Kit
Contains RR13 frame & RR302-4½"
Pro/Doo-Z 2-pack. Great starter kit.

BR403-4½"
Jumbo-Koter Tray
Black recycled plastic 1/2-quart tray; use
with 4½-inch rollers. 15" L x 7¼" W x 3" D.



8619
Pelican® Pail
Fits comfortably in one hand, 1 quart capacity.
Magnet securely holds a brush;
use with 4½" minirollers.



8617
Speed Bucket™
Great for medium-sized jobs, 1/2 gallon capacity.
Magnet securely holds a brush;
use with 6½" minirollers.

Cat. No.	UPC 0-71497-	Description	Shelf Pack	Cubic Ft. Per Pack	Pounds Per Pack
RR393-4½"	14868-1	Jumbo-Koter Pro/Doo-Z kit	10	2.427	8.38
BR403-4½"	14810-0	Jumbo-Koter tray	12	.848	3.72
8619	15237-4	Pelican Pail	6	1.974	6.03
8617	16259-5	Speed Bucket	6	1.518	6.55



Painter's Tip

For a better looking paint job, use a brush to cut-in like usual, but follow immediately with a Jumbo-Koter and roll as close as possible to the edge. Then when the rest of the walls are rolled, you see no cut lines or different textures.



Jumbo-Koter® Minirollers

A Full Constellation of Star Painting Tools

Cat. No.	UPC 0-71497-	Description	Size	Nap	Shelf Pack	Cubic Ft. Per Pack	Pounds Per Pack
RR373	17740-7 17741-4	Pro/Doo-Z® FTP™ 2 pack	4½"	3/16"	12	.215	1.10
RR371	17700-1 17702-5	Pro/Doo-Z FTP 2 pack	4½"	3/8"	12	.215 .376	1.36 1.30
RR372	17701-8 17703-5	Pro/Doo-Z FTP 2 pack	4½"	1/2"	12	.376 .376	1.44 1.78
RR302	14396-9 14397-6	Pro/Doo-Z® 2 pack	4½"	3/8"	12	.215 .376	1.20 1.30
RR602	14398-3 14399-0	Pro/Doo-Z 6 pack	4½"	3/8"	12	.724 1.024	3.38 4.56
RR402	15118-6	Pro/Doo-Z 24 pack	4½"	3/8"	4	1.024	4.34
RR303	14400-3 14401-0	Pro/Doo-Z 2 pack	4½"	1/2"	12	.376 .376	1.38 1.78
RR403	15119-3	Pro/Doo-Z 24 pack	4½"	1/2"	4	1.024	4.24
RR941	17733-9 17735-3	Super/Fab® FTP™ 2 pack	4½"	3/8"	12	.215 .376	1.36 1.84
RR942	17734-6 17736-0	Super/Fab FTP 2 pack	4½"	1/2"	12	.376 .376	1.80 1.80
RR300	14392-1 14393-8	Super/Fab® 2 pack	4½"	3/8"	12	.215 .376	1.36 1.84
RR301	14394-5 14395-2	Super/Fab 2 pack	4½"	1/2"	12	.376 .376	1.44 1.80
RR401	15117-9	Super/Fab 24 pack	4½"	1/2"	4	1.024	5.04
RR309	14930-5 14931-2	Super/Fab 2 pack	4½"	3/4"	12	.473 .571	1.52 2.04
RR409	15122-3	Super/Fab 16 pack	4½"	3/4"	4	1.024	3.74
RR312	15230-5 15231-2	Polar Bear® 2 pack	4½"		12	.215 .376	1.30 1.68
RR305	14407-2 14408-9	50/50™ 2 pack	4½"	1/2"	12	.376 .376	1.17 1.17
RR314	16889-4	Micro Plush™ 2 pack	4½"	5/16"	12	.215	1.34
RR304	14402-7 14403-4	Mohair Blend™ 2 pack	4½"	1/4"	12	.234 .215	1.46 1.54
RR311	15173-5	Red Feather™ 2 pack	4½"	1/4"	12	.234	1.52
RR306	14409-6 14410-2	Super Twist® 2 pack	4½"		12	.234 .376	1.52 1.76
RR606	14411-9 14412-6	Super Twist 6 pack	4½"		12	.724 1.024	4.20 4.90
RR406	15121-6	Super Twist 24 pack	4½"		4	1.024	5.64
RR308	14420-1 14421-8	Pro Foam™ 2 pack	4½"		12	.376 .376	1.36 1.82
RR310	15172-8	Big Green® 2 pack	4½"		12	.376	1.70
RR313	16010-2	Super Doo-Z® 2 pack	4½"	3/8"	12	.215	1.21
RR315	16012-6	Golden Flo™ 2 pack	4½"	3/8"	12	.215	1.19
RR307	14413-3 14417-1	Painter's Choice™ 2 pack	4½"	3/8"	12	.215 .376	1.36 1.66
RR607	14418-8 14419-5	Painter's Choice 6 pack	4½"	3/8"	12	.724 1.024	3.36 4.54

WOOSTER® Jumbo-Koter® Program

ONE SMALL STEP FOR PAINTERS...
ONE GIANT LEAP
FOR QUALITY FINISHES



The Jumbo-Koter system opened a new frontier for miniroller painting. With smooth-spin cage frames that never drag, and miniroller fabrics that create a consistent finish from edge to edge, painters can get surprisingly big results.

Jumbo-Koter® Frames

The key element of the Jumbo-Koter program, these frames have our exclusive, easy-roll cage. The Jumbo-Koter cage spins so smoothly, without skidding up the wall, that some painters feel like they're painting in zero gravity. All 4½- and 6½-inch Jumbo-Koter covers easily dock with any Jumbo-Koter frame!

- Solvent-resistant plastic cage, extra-smooth rolling action
- Both roller sizes fit each frame
- Professional chrome-plated 1/4" shank
- Full-size polypropylene grip with reinforced threads, Sherlock GT® pole compatible

RR013
Jumbo-Koter
12" Frame

There's a Jumbo-Koter frame for every kind of coating mission.



RR028
Jumbo-Koter Shergrip® Frame
Soft, nonslip grip adds comfort & reduces fatigue

R212-4½"
Jumbo-Koter Pipe Painter
Dual cages double production; paints pipes as small as 1-inch diameter

RR323
Jumbo-Koter Flip Frame™
Adjusts in 90-degree increments to smoothly paint challenging areas

RR011
Jumbo-Koter Jr. Frame
Sturdy polypropylene construction, lightweight & affordable

Cat. No.	UPC 0-71497-	Description	Shelf Pack	Cubic Ft. Per Pack	Pounds Per Pack
RR013	14422-5	Jumbo-Koter 12" frame	12	.376	4.61
RR014	14423-2	Jumbo-Koter 27" frame	12	.516	7.94
RR028	17599-1	Jumbo-Koter Shergrip 11" frame	12	.376	4.12
RR113-4½"	16010-2	Jumbo-Koter Shergrip frame & Super Doo-Z® cover	12	.571	5.41
RR115-4½"	16015-7	Jumbo-Koter Shergrip frame & Golden Flo® cover	12	.571	5.41
R212-4½"	17649-3	Jumbo-Koter Pipe Painter	3	.376	1.50
RR323	14607-6	Jumbo-Koter Flip Frame	12	.290	4.48
RR011	16857-3	Jumbo-Koter Jr. 8½" frame	12	.355	2.27

Jumbo-Koter Rollers

Jumbo-Koter rollers are made with Wooster branded fabrics to greatly increase capacity and consistently match finishes to our full-size rollers. Their open, 3/4-inch core makes cleaning easy and refills cost less—unlike other minirollers with built-in bearings that leave craters in tool budgets. For use only with Jumbo-Koter cage frames.



Pro/Doo-Z® FTP™

Double pinstripe no-shed fabric
HydroFlow™ technology offers controlled paint release
All paints (flat to gloss), enamels, primers, urethanes, epoxies

Super/Fab®

Golden yellow, high production fabric
Complete coverage, smooth results
All flat or satin paints, stains, waterproofing

Micro Plush™

White microfiber fabric for smoothest finishes
Great for multiple coats in deep tone colors
All paints & enamels

Super Twist®

Polyamid fabric, super high capacity
Larger yarn pile maximizes pickup
All flat paints, stains, sizings

Super Doo-Z®

White shed-resistant fabric for virtually lint-free finish
Dense fibers reduce dripping & spatter
All paints, enamels, varnishes (satin, velvet, semigloss, gloss)

Pro/Doo-Z®

Golden pinstripe shed-resistant fabric
Finest finish, resists matting
All paints (flat to gloss), enamels, primers, urethanes, epoxies

Polar Bear®

White plush fabric for huge production, reaches into textures
Excels at applying metallic paints
All flat, eggshell or satin paints, stains, sealers, primers

Mohair Blend™

White shed-resistant blend of mohair & polyester
Very smooth finish, added resiliency
All paints, enamels, urethanes, epoxies, floor toppings

Pro Foam™

Charcoal-colored dense foam for lint-free finish
Applies thin coats well
Varnishes, enamels, all paints

Golden Flo™

Yellow fabric offers fast coverage
Low shed, high paint pickup
Flat or eggshell paints, stains, waterproofing

Super/Fab® FTP™

Lager-colored high capacity, shed-resistant fabric
HydroFlow technology offers controlled paint release
All flat, eggshell, satin paints

50/50™

Cream-colored blend of 50% lambswool and 50% polyester
Wool provides maximum capacity; polyester resists matting
All flat, satin, or semigloss paints, stains, waterproofing

Red Feather™

Red, shed-resistant velour for a feather-smooth finish
Perfect for doors, cabinets, metal
All eggshell, semigloss & gloss paints, enamels, urethanes

Big Green®

Lime green flocked foam creates spray-like results
Combines attributes of foam & fiber
Varnishes, stains, all paints

Painter's Choice™

Mint green fabric, economy performance
Easy to load
All flat paints

Meet the Wooster miniroller tools that are designed to make a world of difference when painting.

- Closets • Baths • Kitchens • Baseboards
- Doors • Hallways • Railings • Cutting In

Side Nap vs. Button End

Some painters use minirollers to paint corners, where two adjacent walls or the wall and ceiling are the same color. For this, a cover that has fabric wrapped around the end is needed—a side nap or closed end. Other painters want minis that allow them to paint beside a surface of a different color, or an unpainted surface. In that case, a button end creates a cleaner line and provides greater control. Both roller styles are useful.



RR113-4½"
Jumbo-Koter Shergrip frame & Super Doo-Z cover

RR115-4½"
Jumbo-Koter Shergrip frame & Golden Flo cover



R008
1-Gallon Grid
Paint right from the can with 4½" minirollers. Won't rust; easy to clean. 8½" L x 5" W.

