


PIG® Rip-&-Fit® Absorbent Mat Roll

#MAT243 - Heavy-weight • 15" x 150'



Extra perforations let you customize PIG Mat to the shape you need. Just "rip" it along the easy-tear perfs and "fit" it into place.

- Lasts 2X longer than ordinary mats for fewer change-outs, absorbs everything, works everywhere; that's why more plants worldwide use PIG Mat than any other brand
- Extra perforations in our Rip-&-Fit Mat allow you to easily "rip" this PIG Mat and "fit" it to your application without cutting
- No matter how you rip it, this mat features the proven eight-layer, 100% polypropylene construction of PIG Mat, the strongest mat on the market!
- Exclusive dimple pattern speeds wicking of liquid throughout mat for faster, easier cleanup
- Highly absorbent, fine-fiber construction won't leave behind liquids or fiber residue
- Absorbs most common industrial liquids - oils, water, solvents, coolants and more
- Absorbed leaks and drips blend right in; dark gray color hides grime so mat stays on the job longer
- Flame-resistant material won't burn immediately like cellulose mats; melts when exposed to high heat while on the job
- Perforated every 3.75" across width and every 10" across length
- Heavy-weight construction delivers greater durability and absorbency for demanding tasks and large-volume cleanups

Always in stock. Ships within 24 hours.



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT243 - Pg 1 of 2

MAT243 Specifications

Color:	Gray
Dimensions:	15" W x 150' L
Mat Weight:	Heavy-weight
Fluids Absorbed:	Oils, Coolants, Solvents & Water
Recycled Content:	50% Recycled Content
Absorbency:	Up to 19.6 gal. per bag
Absorbency per:	Up to 19.6 gal. per roll
Dispenser:	No
Perforated:	Every 10" Lengthwise & Every 3.75" Widthwise
Poly-Backing:	No
UV Resistant:	No
Sold as:	1 roll per bag
Weight:	16 lbs.
# per Pallet:	32
Composition:	100% Polypropylene
UNSPSC:	47131901

Technical Information

Warnings & Restrictions:

There are no known warnings and restrictions for this product.

Regulations and Compliance:

29 CFR 1910.22(a)(2) - Floors in the workplace should be, "maintained in a clean and, so far as possible, a dry condition."

Technical Documents:

(Available at newpig.com)

Product Data Sheet (PDS)

Safety Data Sheet (SDS)

Chemical Compatibility (CCG)



MAT243 Metric Equivalent

Dimensions:	38.1cm W x 46m L
Absorbency:	Up to 74.2 L per bag
Absorbency per:	Up to 74.2 L per roll
Weight:	7.3 kg



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304
© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT243 - Pg 2 of 2