

With WOOSTER,
you've got friends in

High Places

WOOSTER[®]

SHERLOCK[®]

EXTENSION POLES

All The Features
Professionals Demand

Quick The green quick-release position lock is made of durable, fiberglass-reinforced nylon with a heavy-duty brass locking pin. Adjust the length of the pole with just a touch of the thumb. You can depend on Sherlock—there's no need to worry about slipping or twisting.

Comfortable The lightweight fiberglass outer pole makes Sherlock easy to handle. It has a polyester fabric surface treatment for durability. The handgrip provides comfortable, non-slip support.

Durable The strong hexagonal inner pole, made of anodized aluminum, prevents twisting and locks in 6-inch increments. The rugged, zinc die cast tip with universal threads holds tools securely.



A No-Twist Aluminum Inner Pole B Thumb-Touch Position Lock C Sturdy Fiberglass Outer Pole D Comfortable Green™ Grip

Cat. No.	UPC 0-71497-	Length	Shelf Pack	Cubic Ft. Per Pack	Pounds Per Pack
R053	66728-1	1' - 2'	6	.190	5.50
R054	66388-7	2' - 4'	6	.286	7.50
R055	66398-6	4' - 8'	6	.554	12.70
R056	66408-2	6' - 12'	3	.440	9.00
R057	66418-1	8' - 16'	3	.613	12.06

Extend Your Profits With WOOSTER

SHERLOCK® POLE DISPLAY

Heighten your business using only about one square foot of floor space and the power of the Wooster name. This compact black wire rack holds 18 Sherlock extension poles, a full shelf pack in each of four different sizes. Complete display includes a bold trilingual sign. Handles of the poles are held off the floor, threaded tips point upward. Rack measures 14½" wide x 11¼" deep x 25½" high. (The rack will also hold Sherlock GT® poles.)

Cat. No.	UPC 0-71497-	Contents (Qty., Cat. No., Size)	Shelf Pack	Cubic Ft. Per Pack	Pounds Per Pack
R850	68570-4	6-R054 2'-4' 6-R055 4'-8' 3-R056 6'-12' 3-R057 8'-16'	1	3.026	53.00

SHERLOCK® MAINTENANCE KIT

Provides convenient field repair of Sherlock threaded extension poles (R053-R057). Complete set of eight parts for spring, tip, or lever replacement. Attractive clamshell package for easy peghook display.



Cat. No.	UPC 0-71497-	Contents (Qty., Cat. No.)	Shelf Pack	Cubic Ft. Per Pack	Pounds Per Pack
FR950	14118-7	1-FR065 Tip 2-FR060 Screws 1-FR066 Lever 1-FR061 Pin 3-FR062 Springs	3	.062	.92



WOOSTER®

The Wooster Brush Company • Wooster, OH • Reno, NV • 800-392-7246 • www.woosterbrush.com