

1100 Series

POLYFOLD FANBACK TRIPLE-BRACE



MODEL 1105 SHOWN



SPECS:

- Features 18-gauge 7/8" round tubular frame
- Three U-shaped double riveted cross braces
- Powder-coated frame
- Double hinges for added stability and durability
- Color coordinated V-tip plugs for added stability
- Color coordinated polypropylene glides
- Features our unique full size double contoured high fanback and waterfall seat
- Stacks up to 26 high on DY1100 Dolly horizontally

DIMENSIONS:



OVERALL: 34 1/2"H X 18 1/2"W X 20 3/4"D
FOLDED: 44"H X 18 1/2"W X 2 1/4"D
SEAT: 17 3/4"H X 15 3/4"W X 16"D
BACK: 13 1/2"H X 18 1/2"W



480lb. weight capacity!

PLASTIC / FRAME COMBINATIONS

- #1105** BLUE PLASTIC / GREY FRAME
- #1108** ROSE PLASTIC / BRONZE FRAME
- #1110** BLACK PLASTIC / BLACK FRAME
- #1121** WHITE PLASTIC / WHITE FRAME



EXT-8 Extension Bar required for 1100 Series on Model #84 (88" DOOR HEIGHT CLEARANCE)

USE WITH:

Model #EXT-8 Extension Bar for Model #84

Model #84 Double-Tier Hanging Chair Truck

CAPACITY: HOLDS UP TO 84 FOLDING CHAIRS (1100 SERIES) WITH EXT-8

Model #DY35/#DY50 Folding Chair Dolly

CAPACITY: DY35 HOLDS UP TO 30 FOLDING CHAIRS (1100 SERIES) DY50 HOLDS UP TO 42 FOLDING CHAIRS (1100 SERIES)

FOR VERTICAL FOLDING STORAGE

Model #1100 Folding Chair Dolly

CAPACITY: HOLD'S UP TO 26 FOLDING CHAIRS (1100 SERIES) **FOR HORIZONTAL FOLDING STORAGE**

AVAILABLE ACCESSORIES



National Public Seating

