

# TWO- & FOUR-WHEEL SNACK TRUCKS

Modular All-Aluminum Hand Truck Is Designed To Move Light, Bulky Loads With Fewer Trips!

## Two-Wheel Snack Truck

### TWO-WHEEL SPECIFICATIONS

Overall width (as shown)	17"
Overall height	61-½"
Weight	28 lbs.
Capacity (with nose extended)	80 lbs.
Capacity (with nose folded)	500 lbs.



P/N	Wt.(lbs.)
HSA811AA1--5	28.0

With 44" nose extension.

## Four-Wheel Snack Truck

### FOUR-WHEEL SPECIFICATIONS

Overall width (as shown)	17"
Frame width	12"
Overall width	17-¼"
Overall height	73"
Weight	34 lbs.
Four-wheel bed length	66-½"
Wheels (standard)	8" mold-on rubber
Swivel casters with brakes	5"
Folding nose length	36"
Folding nose capacity (in two-wheel position)	80 lbs.
Four-wheel capacity	200 lbs.



P/N	Wt.(lbs.)
STA8AA1	34.0

With 815 wheels & folding nose.

Patent # D475,167 and D593,722

## ACCESSORIES



P/N	Wt.(lbs.)
86006	2.5

Heavy-duty cast stair climbers with replaceable low-friction polymer glide bars.



P/N	H"	Wt.(lbs.)
40050	55	1.5
40010	60	1.5
40011	68	2.5

Hi-U frame extensions add height and stability for taller loads. (hardware required)



P/N	L"	Wt.(lbs.)
302154	36	5.0
302147	44	6.0

Optional nose extension supports up to 80 pounds.