

1200 Series

VINYL PREMIUM



products meet or exceed applicable ANSI/BIFMA standards



MODEL 1203 SHOWN



480lb. weight capacity!

SPECS:

- Features 18-gauge 7/8" round tubular frame
- Two U-shaped double riveted cross braces
- Powder-coated frame
- Double hinges for added stability and durability
- Color coordinated V-tip plugs for added stability
- Color coordinated polypropylene glides
- Features our unique full size double contoured back and waterfall seat
- Fully upholstered seat and back
- Vinyl and Foam are Cal 117 rated
- .80MM Vinyl over 1 1/4", 0.9lb. density foam seat and 1.2lb. density back

DIMENSIONS:

OVERALL: 29 1/2"H X 18 3/4"W X 20 1/4"D

FOLDED: 38"H X 18 3/4"W X 2 1/2"D


SEAT: 17 3/4"H X 16"W X 16"D

BACK: 8 3/4"H X 18 3/4"W

CAL-117 RATED

VINYL / FRAME COMBINATIONS

- #1201** FRENCH BEIGE VINYL / BEIGE FRAME
- #1202** WARM GREY VINYL / GREY FRAME
- #1203** HONEY BROWN VINYL / BEIGE FRAME
- #1204** DARK MIDNIGHT BLUE VINYL / CHAR-BLUE FRAME
- #1210** CAVIAR BLACK VINYL / BLACK FRAME



USE WITH:

Model #84 Double-Tier Hanging Chair Truck

CAPACITY: HOLDS UP TO 84 FOLDING CHAIRS (1200 SERIES)

Model #DY35/#DY50 Folding Chair Dolly

CAPACITY: DY35 HOLDS UP TO 35 FOLDING CHAIRS (1200 SERIES)
DY50 HOLDS UP TO 50 FOLDING CHAIRS (1200 SERIES)

FOR VERTICAL FOLDING STORAGE



AVAILABLE ACCESSORIES



National Public Seating



800.261.4112 | www.nationalpublicseating.com