

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-501

INTERCEPT TECHNOLOGY® with DuPont™ Kevlar® Stretch Armor exclusively from Ansell

MD

Medium Duty



Cut-Protection

Superior cut protection and dexterity when workers need high levels of protection with optimal productivity, the HyFlex 11-501 glove is the answer

- Ansell's HyFlex 11-501 glove is designed to significantly raise the standards of protection and dexterity for cut-resistant gloves. This achievement has been made, thanks to Ansell's INTERCEPT TECHNOLOGY®
- The HyFlex 11-501 glove is also resistant to heat, allowing versatile use
- When workers need high levels of protection with optimal productivity, the HyFlex 11-501 glove is the answer



Industries

- Aerospace
- Appliance Manufacturing
- Automotive
- General Carpentry
- General Industry
- Glass
- HVAC/Sheet Metal Users/Window Glazers
- Lumber/Wood/Paper
- Metal Fabrication
- Metalworking
- Plastics
- Plumbers
- Public Utilities

Applications

- Forming, machining and bending of small sharp parts
- Handling glass or slippery plastics
- Handling slitter blades and utility knives
- Handling smooth, slippery or sharp-edged materials like glass, sheet metal, tile and veneer

Performance Profile

- Enhanced cut protection, reduces the risk of injury and related expenses.
- High cut protection increases worker confidence and morale when handling sharp objects.
- Provides barehand closeness, reducing risk of snags and hang-ups.
- Enhances grip in light oil conditions.

Key Features

- Features INTERCEPT TECHNOLOGY® with DuPont™ Kevlar® Stretch Armor exclusively from Ansell.
- Product provides: ISO Level D.
- Ergonomic design provides barehand closeness and reduces hand fatigue.
- Nitrile foam coating enhances light oil grip, solid dry grip and tactile sensitivity.
- Available in a wide range of sizes to protect more workers.

Technologies



DuPont™
KEVLAR®

Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	GAUGE	SIZE	LENGTH	COLOR	PACKAGE
HyFlex 11-501	Type: Palm coated Coating material: Foam nitrile Liner material: Lycra® Kevlar Ansell INTERCEPT Technology Cuff style:Knitwrist	13	6 - 11	206-260 mm 8.11-10.23 inches	Blue and heather grey	12 pairs/bag, 12 bags/carton

Europe, Middle East & Africa

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
+32 2 528 74 00
+32 2 528 74 01

North America

Ansell Healthcare Products, LLC
111 Wood Avenue South
Suite 210
Iselin, NJ 08830, USA
+1 800 800 0444
+1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
+61 1800 337 041
+61 1800 803 578

Asia Pacific

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
63000 Cyberjaya
Selangor, Malaysia
T: +60 3 83106688
F: +60 3 8318 6699

Latin America & Caribbean

Ansell Brazil Ltda.
Rua das Figueiras 474 - 4º Andar
Bairro Jardim
SP 09080-300 Santo André
Brazil
CNPJ: 03.496.778/0001-21
+55 11 3356 3100

Russia

Анселл РУС
123610 Россия, Москва
Краснопресненская
Наб. 12, п.3, оф. 1304А
Тел. +7 495 258 13 16

Ansell, * and ™ are trademarks owned by Ansell Limited or one of its affiliates, except as noted. DuPont™ and Kevlar® are trademarks of DuPont used under license. Lycra® is a trademark owned by INVISTA. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2016 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.