

WeldSkill® WM 400 Amp Air-Cooled MIG Gun



60% Duty Cycle - CO₂ Carbon Dioxide

Suitable for Medium Duty Fabrication.

FEATURES

- **Oval Handle Shape** reduces operator fatigue
- **Dependable Welding** for a wide variety of industrial applications
- **High Impact-Resistant Handle and Components** for long-lasting durability
- **Three-Layer Conductor Tube Construction** (copper tube/silicon-resin glass insulator/metal jacket) for improved electrical conductivity
- **Improved Performance** with longer life consumables
- **Heavy Duty Design** with operator appeal

Tweco® Style Rear Connector

Adapter kits are available to fit Tweco rear connection to most wire feeders

Wire Size	Length	Part No.	Stock No.
Up To .045" (1.2 mm)	12 ft (3.6 m)	WM400-12-3545	1047-1001
	15 ft (4.6 m)	WM400-15-3545	1047-1002
Up To 1/16" (1.6 mm)	15 ft (4.6 m)	WM400-15-116	1047-1007
	15 ft (4.6 m)	WM400-15-116K4\$	1040-1170
	25 ft (7.6 m)	WM400-25-116	1047-1016

Miller® Style Rear Connector

Wire Size	Length	Part No.	Stock No.
Up To .045" (1.2 mm)	15 ft (4.6 m)	WM400M-15-3545	1047-1027
	12 ft (3.6 m)	WM400M-12-116	1047-1031
Up To 1/16" (1.6 mm)	15 ft (4.6 m)	WM400M-15-116	1047-1032
	15 ft (4.6 m)	WM400M-15-116K4\$	1040-1171
	25 ft (7.6 m)	WM400M-25-116	1047-1019

Part No. MSAK354 (Stock No. 2642-2470) Control wire assembly furnished.

Lincoln® Style Rear Connector

Fits Lincoln LN7, 8, 9, SP200

Wire Size	Length	Part No.	Stock No.
Up To .045" (1.2 mm)	15 ft (4.6 m)	WM400L-15-3545	1047-1077
	15 ft (4.6 m)	WM400L-15-116	1047-1082
Up To 1/16" (1.6 mm)	15 ft (4.6 m)	WM400L-15-116K4\$	1040-1172
	25 ft (7.6 m)	WM400L-25-116	1047-1022


Some Lincoln wire feeders are assembled with their K1500-2 gun receiving bushing that will accept Tweco Style MIG Guns direct from the factory. Control wire Part No. MS354-DSLJ (Stock No. 2606-2137) must be ordered separately.

Part No. LAK354 (Stock No. 2642-2450) Control wire assembly furnished.

Euro-Kwik Style Rear Connector

Wire Size	Length	Part No.	Stock No.
Up To .045" (1.2 mm)	15 ft (4.6 m)	WM400X-15-3545	1047-1052
1/16" (1.6 mm)	15 ft (4.6 m)	WM400X-15-116	1047-1057

§ Suffix "K4" = Kucklehead Conductor Tube – Part No. 64SFLX480 (Stock No. 1640-1113)



Rated Output			Wire Size	Cooled	Application Usage
Amps	Duty Cycle	Gas			
400 Amps	60%	CO ₂ Carbon Dioxide	Up To 1/16" (1.6 mm)	Air	Medium Duty Fabrication

Miller is a registered trademark of Illinois Tool Works, Inc. Lincoln is a registered trademark of Lincoln Electric Co. The aforementioned registered trademarks are in no way affiliated with Tweco. Tweco is registered trademark of ESAB.



EASY FIND GUIDE

See Page 152 for Replacement Parts & Optional Accessories