

P-628

Shurtape®
TRUE TO YOUR WORK™

PROFESSIONAL GRADE, COATED GAFFER'S TAPE

TYPICAL APPLICATIONS

- For general use in the convention, hospitality, exhibition and trade show industries, as well as for bundling wires, taping down lighting and props, and masking silk screen frames in the audio/visual, television, photography, theatrical and motion picture industries
- Can also be used for protection and book-binding, color-coding, labeling and stage marking

PRODUCT FEATURES

- High tack, tensile strength and holding power
- Writable surface
- Durable and conformable
- Hand-tearable in machine and cross directions

CONSTRUCTION

Overall Grade/Function: Professional
Backing: Matte-finish coated cloth
Adhesive: Synthetic rubber

STANDARD WIDTH(S)

48 mm 72 mm


STANDARD LENGTH(S)

50 m
Contact your Shurtape sales representative for other available sizes

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

COLOR(S)



PHYSICAL PROPERTIES STANDARD METRIC

Tensile Strength	50 lbs/in width	87.6 N/10 mm
Adhesion to Stainless Steel	75 oz/in width	8.21 N/10 mm
Thickness	10.75 mils	0.27 mm
Elongation	4%	4%
Service Temperature Range	50 F to 200 F	10 C to 93 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

