

# PROVOQ®

Superior Comfort And Fit



Part	Lens	Part	Lens
S7210S••	Clear	S7255S•	Multi-Color
S7210ST••	Clear Anti-Fog	S7260S•	Infinity Blue
S7220S••	Gray	S7270S••	Silver Mirror
S7220ST••	Gray Anti-Fog	S7275S••	Blue Mirror
S7230S••	Amber	S7280S••	Indoor/Outdoor Mirror
S7240S••	Orange	S7280ST•	Indoor/Outdoor Anti-Fog Mirror

- Superior comfort and fit.
- Soft nose piece provides comfort fit.
- Rubber temples provides non-slip comfort.
- Offer 99.9% protection against harmful UV rays.
- Lenses are coated for superior scratch resistance.
- Economical lightweight glasses offer superior protection.

## GENERAL SPECIFICATION

Bridge: 16.66mm
Closest Point Between Lens: 8.18mm
Closest Point Between Strap Holding Parts: 79.35mm
Lens Base: 9 curve
Lens Size Diagonal: 79.83mm
Lens Size Vertical: 41.12mm
Lens Thickness: 2.4mm
Overall Length (Lens-Tip): 158mm
Overall Width: 136mm
PD: 64mm
Weight: 24.9g













## PACKAGING

Polybag: 1pc

Inner Box: 12 pcs

Case: 300 pcs

COMPONENT	MATERIAL	FEATURES
Lens	Polycarbonate	9 base curve
Frame	N/A	N/A
Nose Piece	TPR	N/A
Sleeve (on temple)	TPR	Integral to temple
Temple	Polycarbonate	Streamlined design
Hinge	Polycarbonate	Integral to temple
Screw	Plated steel	Standard hinge screw

PART	LENS	LENS MARKING	FRAME MARKING
S7210S	 Clear	P Z87 + U6	P Z87 + / P c SEI CAN/CSA Z94.3-07
S7210ST	 Clear Anti-Fog	P Z87 + U6	P Z87 + / P c SEI CAN/CSA Z94.3-07
S7220S	 Gray	P Z87 + U6 L3	P Z87 + / P c SEI CAN/CSA Z94.3-07
S7220ST	 Gray Anti-Fog	P Z87 + U6 L3	P Z87 + / P c SEI CAN/CSA Z94.3-07
S7230S	 Amber	P Z87 + S	P Z87 + / P c SEI CAN/CSA Z94.3-07
S7240S	 Orange	P Z87 + S	P Z87 + / P c SEI CAN/CSA Z94.3-07
S7255S	 Multi-Color Mirror	P Z87 + S	P Z87 +
S7260S	 Infinity Blue	P Z87 + S	P Z87 +
S7270S	 Silver Mirror	P Z87 + S	P Z87 + / P c SEI CAN/CSA Z94.3-07
S7275S	 Blue Mirror	P Z87 + S	P Z87 + / P c SEI CAN/CSA Z94.3-07
S7280S	 Indoor/Outdoor Mirror	P Z87 + U6 L1.7	P Z87 + / P c SEI CAN/CSA Z94.3-07
S7280ST	 Indoor/Outdoor Anti-Fog Mirror	P Z87 + U6 L1.7	P Z87 +

## LENS MARKING

### Symbols:

P: Manufacturer's mark

Z87: ANSI standard for Eye and Face protection devices

+: High Impact

H: Small Head Size

S: Special Purpose

### UV Filter Transmittance:

U2: Max Effective Far UV= .1% / Max Near UV= 3.7%

U2.5: Max Effective Far UV= .1% / Max Near UV= 2.3%

U3: Max Effective Far UV= .07% / Max Near UV= 1.4%

U4: Max Effective Far UV= .04% / Max Near UV= .5%

U5: Max Effective Far UV= .02% / Max Near UV= .2%

U6: Max Effective Far UV= .01% / Max Near UV= .1%

### Visible Light Filters:

L1.3: 85% Max. Visible Light

L1.7: 55% Max. Visible Light

L2.5: 29% Max. Visible Light

L3: 18% Max. Visible Light

## FRAME MARKING

### Symbols:

P: Manufacturer's mark

Z87: ANSI standard for Eye and Face protection devices

+: High Impact

P c SEI CAN/CSA Z94.3-07: CAN/CSA for protection devices