




MC CABLE SADDLE/SCREW TYPE CONNECTORS

Cable Connectors Steel
N/A

B72



Catalog #: 2800

APPLICATIONS

For use in dry locations for connecting MCI, MCI-A (2800 only), AC, and HCF cable into a box or enclosure
N/A

PRODUCT FEATURES

- Easy to install - just tilt, insert, and snap down
- Tri-head screw/clamp design - connector can be installed by using a slotted, Phillips, or Robertson head screwdriver
- Integral insuliner provides maximum wire protection
- Durable all-steel construction
- Zinc electro plated for corrosion protection

UL LISTED

File E195966

GENERAL PRODUCT INFORMATION

Trade Size: 1/2 in.

DRAWING DIMENSIONS

Dimension A: 1-7/16 in.
 Dimension B: 7/8 in.
 Dimension C: 7/16 in.

PACKAGING

Package Type: Carton
 Std. Pkg.: 50
 Ship Carton Qty.: 500
 Product UPC-A Labeled: No
 Weight (Lbs. Per/C): 8.00
 Ship Carton Length (in.): 17.30
 Ship Carton Width (in.): 11.90
 Ship Carton Height (in.): 6.50
 Ctn Weight (Lbs.): 40.50
 UPC Number: 050169028001
 I2of5: 50050169028006