# Millermatic 252

### **MIG Power Source**, **Wire Feeder and Gun Package**



### Quick **Specs**

### Industrial **Applications**

Metal fabrication Maintenance and repair Farm/home Light industrial

#### **Processes**

MIG (GMAW) Flux-cored (FCAW)

### **Input Power**

200(208)/230 V, single-phase, 60 Hz 230/460/575 V, single-phase, 60 Hz

Amperage Range 30-300 A

Rated Output 200 A at 28 VDC, 60% duty cycle 250 A at 28 VDC, 40% duty cycle

Wire Feed Speed 50-700 ipm (1.3-17.8 m/min.)

Max. Open-Circuit Voltage 38 V

**Net Weight** 207 lb. (94 kg)

Highest output in its class (250 A at 28 VDC). Weld longer on high-end applications.

Infinite voltage control with self-calibrating digital meters that permit presetting of voltage and wire feed speed. Ensures precise parameters and accuracy.

Integrated digital timers come complete with presettable preflow/ postflow, burnback, spot and delay (stitch) timers. Independent timers for MIG and spool gun.

Line voltage compensation

keeps power constant even if power input varies by ±10 percent.

### Active Arc Stabilizer™

minimizes weld cleanup, and provides excellent starts proven superior to the competition.

Auto Gun Detect™ allows operator to simply pull trigger on MIG gun, spool gun or push/pull gun. Automatically detects and recalls the voltage, wire feed speed and timer of the active gun. See page 3 for more information.




### Comes complete with:

- 15 ft. (4.6 m), 250-amp MDX<sup>™</sup>-250 MIG gun
- 10 ft. (3 m) work cable with clamp
- 10 ft. (3 m) industrial power cord (with plug on 200/230 V model)
- Flow gauge regulator and gas hose for argon or AR/CO<sub>2</sub> mix
- Factory-installed lowered running gear/ cylinder rack
- .030/.035 in. reversible dual-groove drive rolls
- Extra contact tips



the first time with convenient flip-down compartment that provides fast access to parameter chart and consumables. See page 3 for more information.



Fan-On-Demand™ cooling system only operates when needed, reducing noise. energy use and the amount of contaminants pulled though the machine.



Now with NEW! MDX Series MIG gun. Superior aluminum MIG welding with direct connection of optional spool guns and push-pull guns. Directly connect your Spoolmate™ 200 and Spoolmatic® spool guns or XR™ push-pull guns. No extra module to buy or install.



Welder is warranted for three years, parts and labor. Original main power rectifier parts are warranted for five years. Gun warranted for 90 days, parts and labor.



### Miller Electric Mfg. LLC

An ITW Welding Company 1635 West Spencer Street P.O. Box 1079 Appleton, WI 54912-1079 USA

### **Equipment Sales US and Canada**

Phone: 866-931-9730 FAX: 800-637-2315

International Phone: 920-735-4554 International FAX: 920-735-4125











## **Specifications** (Subject to change without notice.)







Amperage Range	Rated Output	Amps Input 200(208) V				KW	Wire Feed Speed	Wire Type and Diameter	Max. Spool Size	Max. Open- Circuit Voltage	Dimensions	Net Weight
30-300 A	200 A at 28 VDC, 60% duty cycle 250 A at 28 VDC, 40% duty cycle	48 2.3*	42 2*	21 1*	17 0.8*	 7.5 0.13*	50–700 ipm (1.3–17.8 m/min.)	Solid/stainless steel: .023045 in. (0.6-1.2 mm) Flux-cored: .030045 in. (0.8-1.2 mm)	12 in. (305 mm)	38	H: 30 in. (762 mm) W: 19 in. (483 mm) D: 40 in. (1,016 mm)	207 lb. (94 kg)


<sup>\*</sup>While idling.

Note: Operating temperature range: -4° to +104° F (-20° to +40° C). Storage temperature range: -22° to +122° F (-30° to +50° C).




Certified by Canadian Standards Association to both the Canadian and U.S. Standards.


### **Control Panel**



- 1. Voltmeter
- 2. Voltage Control
- 3. Wire Speed Meter
- 4. Wire Speed Control

### **Performance Data**







### **Standard Fully Loaded Features**

### **EZ-Change™ low cylinder rack**

■ Operators no longer need to lift cylinders. Cylinders now easily roll on and off our EZ-Change™ low cylinder rack.

### **Angled wire drive**

- Angled industrial aluminum dual-gear drive system significantly improves wire feeding and runs large spools of wire.
- Allows quick change of drive rolls without tools.
- Drive roll storage no more lost drive rolls, extra drive rolls are conveniently stored next to drive motor.
- Operators no longer bump into and bend MIG gun and gun liner.

### **Dual front handles**

- Split handle with rubber grips designed to move machine easily and allow work lead and MIG gun to be stored independently.
- Handles provide protection for front panel and MIG gun during transportation.

# EZ-Access™ consumable compartment and parameter chart

 Convenient flip-down compartment holds parameter chart and storage for consumables.

### **Auto-Gun Detect™**

- Simply pull the trigger for either the MIG, spool gun or any Miller® push-pull gun. The Millermatic 252 automatically recalls voltage, wire feed speed and timer of the active gun.
- Reduces setup time!























### **Optional Fully Loaded Features**

### **Elevated gun and cable rack**

#### 300335

- Tangle-free, independent way to store spool gun cables, keeping them off of the floor.
- No more running over spool gun cables or cables dragging on the floor.
- Elevated gun and cable rack can be used with either a single or dual cylinder rack. (Elevated gun and cable rack is included with the dual EZ-Change<sup>™</sup> low cylinder rack.)



# Dual EZ-Change™ low cylinder rack with elevated gun and cable rack

### 300337

- Dual cylinder rack allows for easy storage of two cylinders.
- EZ-Change™ low cylinder rack eliminates the need to lift cylinders on and off cylinder rack.
- No more running over spool gun cables or cables dragging on the floor.
- Tangle-free, independent way to store spool gun cables, keeping them off of the floor.





### **Genuine Miller® Accessories**



### **Dual EZ-Change™ Low Cylinder Rack with** Elevated Gun and Cable Rack 300337

Dual cylinder rack allows operators to easily roll cylinders on and off the rack with no lifting. Gun and cable rack keeps cables off the floor and tangle free.

### Elevated Gun and Cable Rack 300335

For use with single cylinder rack. (Included with dual EZ-Change low cylinder rack.)



Protective Cover 195142

Features side pocket. (Not for use with dual cylinder rack or elevated gun and cable rack.)

### Argon/Mixed Gas Regulator and Gas Hose 195050



Female Receptacle



Full KVA Adapter Cord 300517 Field NEMA 14-50P to NEMA 6-50R. Adapts engine drive 120/240 V plug to common Millermatic® and Spectrum® 240 V plug.

### MIG Guns



### MDX™-250 MIG Gun

with AccuLock™ MDX Consumables

**1770035** 10 ft. (3 m) **1770036** 12 ft. (3.7 m)

1770037 15 ft. (4.6 m), standard

Industrial 250-amp MIG gun with consumables for .030/.035 in. (0.8/0.9 mm) wire.

### MDX™-250 MIG Gun

with Industrial AccuLock™ S Consumables

**1770041** 10 ft. (3 m) **1770042** 12 ft. (3.7 m)

**1770043** 15 ft. (4.6 m)

Industrial 250-amp MIG gun with consumables for .035/.045 in. (0.9/1.2 mm) wire.

### **Spool Guns**



### Spoolmatic® 15A Spool Gun 195156 Spoolmatic® 30A Spool Gun 130831

Ideal for aluminum welding jobs. Air-cooled, one-pound spool gun with 15-foot (4.6 m) or 30-foot (9.1 m) cable assembly. Rated at 200 amps at 100 percent duty cycle. For detailed information, see Spoolmatic literature M/1.73.



### Spoolmate™ 200 Spool Gun 300497

Reliable and economical spool gun perfect for hobbyists and light fabricators who weld aluminum. Handles .030-.035 inch (0.8-0.9 mm) aluminum wires and .023-.035 inch (0.6-0.9 mm) steel/stainless steel wires. Rated at 160 amps, 60 percent duty cycle with 20-foot cable assembly. For detailed information, see Spoolmate literature M/1.47.

### Optional Spoolmate™ 200 Head Tubes

**300591** 45-degree head tube

**300592** 9-inch extension head tube

**243385** 5-inch head tube

### **Push-Pull Guns**



### XR-Aluma-Pro™ Lite Push-Pull Gun

**300948** 25 ft. (7.6 m)

Air-cooled gooseneck-style gun for .030-.047 in. (0.8-1.2 mm) aluminum. Rated at 175 amps at 60 percent duty cycle.



#### XR-Aluma-Pro™ Push-Pull Gun

**300000** 15 ft. (4.6 m)

**300001** 25 ft. (7.6 m)

Air-cooled gooseneck-style gun for .030-.047 in. (0.8-1.2 mm) aluminum. Rated at 300 amps at 100 percent duty cycle.

### **U-Grooved Aluminum Drive Roll** and Accessory Kits for XR-Aluma-Pro **Push-Pull Guns**

**195311** .035 in. (0.9 mm)

**195313** .047 in. (1.2 mm)

Kits include Millermatic U-grooved drive rolls, nylon wire guides and contact tips.



### **Consumables**

### For MDX™-250 MIG Guns

### Standard Miller® AccuLock™ MDX Consumables

Smaller consumables and components to access hard-to-reach weldments.

### Contact Tips (10 per package)

T-M023 .023 in. (0.6 mm) T-M030 .030 in. (0.8 mm) T-M035 .035 in. (0.9 mm) T-M045 .045 in. (1.2 mm)

#### **Nozzles**

N-M1200C Copper, 1/2 in. ID, flush, standard N-M1218C Copper, 1/2 in. ID, 1/8 in. recess **N-M5800C** Copper, 5/8 in. ID, flush

**N-M5818C** Copper, 5/8 in. ID, 1/8 in. recess N-M58XTC Copper, 5/8 in. ID, 1/8 in. stickout

Diffuser D-M250

### **Monocoil Replacement Liners**

#### 10 ft. Liner

LM1A-10 .023/.025 in. (0.6 mm) LM2A-10 .030/.035 in. (0.8/0.9 mm) LM3A-10 .035/.045 in. (0.9/1.2 mm)

### 12 ft. Liner

LM1A-12 .023/.025 in. (0.6 mm) LM2A-12 .030/.035 in. (0.8/0.9 mm) LM3A-12 .035/.045 in. (0.9/1.2 mm)

15 ft. Liner

LM1A-15 .023/.025 in. (0.6 mm) LM2A-15 .030/.035 in. (0.8/0.9 mm) LM3A-15 .035/.045 in. (0.9/1.2 mm)

#### Optional Bernard® AccuLock™ S Consumables

Consumables for increased durability and longer life when guns are used in industrial applications.

### Contact Tips (10 per package)

**T-A023CH** .023 in. (0.6 mm) T-A030CH .030 in. (0.8 mm) T-A035CH .035 in. (0.9 mm) T-A039CH .039 in. (1.0 mm) T-A045CH .045 in. (1.2 mm)

#### **Nozzles**

N-A5800C Copper, 5/8 in. ID, flush, standard N-A5818C Copper, 5/8 in. ID, 1/8 in. recess

N-A5814C Copper, 5/8 in. ID, 1/4 in. recess

Diffuser D-MA250

Note: Miller® FasTip™, M-Series and Bernard Centerfire™ diffusers and consumables are NOT compatible with MDX Series guns.

### For Spoolmatic® Spool Guns and **XR<sup>™</sup> Push-Pull Guns**

#### For Aluminum Wire

FasTip™ Contact Tips (25 per package) **206186** Heavy-duty, .030 in. (0.8 mm) 206187 Heavy-duty, .035 in. (0.9 mm) 206188 Heavy-duty, .040 in. (1.0 mm) 206189 Heavy-duty, 3/64 in. (1.2 mm) Heavy-duty, 1/16 in. (1.6 mm) 206191 209026 Tapered, .030 in. (0.8 mm) 209027 Tapered, .035 in. (0.9 mm) **209029** Tapered, 3/64 in. (1.2 mm) 206030 Tapered, 1/16 in. (1.6 mm)

#### Screw-On Nozzles

**199610** Brass, 1/2 in. orifice, tapered **199613** Brass, 5/8 in. orifice, tapered 199614 Brass, 5/8 in. orifice, tapered HD 199611 Brass, 3/4 in. orifice, straight 199612 Brass, 3/4 in. orifice, straight HD 209035 Copper, 3/8 in. orifice, tapered 199615 Copper, 1/2 in. orifice, tapered 209036 Copper, 1/2 in. orifice, tapered HD **198855** Copper, 5/8 in. orifice, tapered **199618** Copper, 5/8 in. orifice, tapered HD **207313** Copper. 5/8 in. orifice, tapered 15/16 OD 199616 Copper, 3/4 in. orifice, straight 199617 Copper, 3/4 in. orifice, straight HD

### Bernard® Centerfire™ "T" Series Contact Tips

**T-035AL** .035 in. (0.9 mm) T-047AL .047 in. (1.2 mm) T-062AL 1/16 in. (1.6 mm)

### Bernard® Centerfire™ Small Nozzles

**NST-3818B** Brass, 3/8 in. ID, 1/8 in. tip recess NS-1218B Brass, 1/2 in. ID, 1/8 in. tip recess NS-1200B Brass, 1/2 in. ID, flush tip NS-5818B Brass, 5/8 in. ID, 1/8 in. tip recess NS-1218C Copper, 1/2 in. ID, 1/8 in. tip recess

### For Spoolmate 200 Spool Gun

Note: Spoolmate 200 spool gun ships with (2) .030 in. and (2) .035 in. contact tips and (1) nozzle.

### For Standard Heavy-Duty Head Tube

Contact Tips (5 per package) **199387** .030 in. (0.8 mm)

199388 .035 in. (0.9 mm)

**Nozzle 050622** 

### For Optional Head Tubes

Note: The same consumables are used on 45-degree, 5-inch, and 9-inch extension head tubes.

#### Contact Tips (5 per package)

**199730** .024 in. (0.6 mm)

(requires V-knurled drive roll 136135)

**186419** .030 in. (0.8 mm)

**186406** .035 in. (0.9 mm)

Nozzle 186405

### For Millermatic® 252

Note: Machine drive roll kits include two drive rolls and an inlet guide.

#### V-Grooved Drive Roll Kits (solid wire)

**204579** .030 and .035 in. (0.8 and 0.9 mm) combination (reversible)

**087131** .024 in. (0.6 mm)

079594 .030 in. (0.8 mm)

**079595** .035 in. (0.9 mm)

**079596** .045 in. (1.2 mm)

#### V-Knurled Drive Roll Kits

(flux-cored or difficult-to-feed wire)

**079606** .035 in. (0.9 mm)

**079607** .045 in. (1.2 mm)

U-Grooved Drive Roll Kits (aluminum wire)

**044749** .035 in. (0.9 mm) **079599** .047 in. (1.2 mm)



## **Ordering Information**

<b>Steel Configuration</b>	Stock No.	Description	Qty.	Price
Millermatic® 252	907321	200(208)/230 V, 60 Hz		
	907322	230/460/575 V, 60 Hz		
Millermatic V-Grooved Drive Roll Kits (solid wire)	087131	.024 in. (0.6 mm)		
	079594	.030 in. (0.8 mm)		
	079595	.035 in.(0.9 mm)		
	079596	.045 in.(1.2 mm)		
Millermatic V-Knurled Drive Roll Kits (flux-cored)	079606	.035 in. (0.9 mm)		
	079607	.045 in. (1.2 mm)		
Miller® AccuLock™ MDX™ Contact Tips	T-M023	.023 in. (0.6 mm)		
(10 per package)	T-M030	.030 in. (0.8 mm)		
	T-M035	.035 in. (0.9 mm)		
	T-M045	.045 in. (1.2 mm)		
Miller® AccuLock™ MDX™ Nozzles	N-M1200C	Copper, 1/2 in. ID, flush, standard		
	N-M1218C	Copper, 1/2 in. ID, 1/8 in. recess		
	N-M5800C	Copper, 5/8 in. ID, flush		
	N-M5818C	Copper, 5/8 in. ID, 1/8 in. recess		
	N-M58XTC	Copper, 5/8 in. ID, 1/8 in. stickout		

### **Aluminum Configuration (Spool Gun)** For MDX-250 gun consumables and non-aluminum Millermatic 252 drive rolls, see steel configuration chart above.

Millermatic® 252 Spool Gun Packages (includes standard MDX™-250 MIG gun)	951066	200(208)/230 V, 60 Hz with Spoolmatic® 30A, dual cylinder rack, elevated gun and cable rack, regulator and hose	
	951065	230/460/575 V, 60 Hz with Spoolmatic® 30A, dual cylinder rack, elevated gun and cable rack, regulator and hose	
Spoolmatic® Contact Tips (10 per package)	206187 206188 206189	.035 in. (0.9 mm) .040 in. (1.0 mm) .047 in. (1.2 mm)	
Spoolmatic® Nozzles	198855 199618 199616 199617	5/8 in. (16 mm) diameter 5/8 in. (16 mm) diameter, HD 3/4 in. (19 mm) diameter 3/4 in. (19 mm) diameter, HD	

### Aluminum Configuration (Push-Pull Gun) For MDX-250 gun consumables and non-aluminum Millermatic 252 drive rolls, see steel configuration chart above.

Millermatic® 252	907321	200(208)/230 V, 60 Hz
(includes standard MDX™-250 MIG gun)	907322	230/460/575 V, 60 Hz
XR-Aluma-Pro™ Lite Gun (air-cooled)	300948	25 ft. (7.6 m)
XR-Aluma-Pro™ Gun (air-cooled)	300000	15 ft. (4.6 m)
	300001	25 ft. (7.6 m)
Millermatic U-Grooved Drive Roll Kits (aluminum)	044749	.035 in. (0.9 mm)
	079599	.047 in. (1.2 mm)
XR-Aluma-Pro U-Grooved Drive Roll Kits	195311	.035 in. (0.9 mm)
(required, includes Millermatic U-Grooved Drive Roll Kit)	195313	.047 in. (1.2 mm)
XR-Aluma-Pro Lite Contact Tips (10 per package)	T-035AL	.035 in. (0.9 mm)
	T-047AL	.047 in. (1.2 mm)
XR-Aluma-Pro and XR-Pistol Contact Tips (10 per package)	206187	.035 in. (0.9 mm)
	206188	.040 in. (1.0 mm)
	206189	.047 in. (1.2 mm)
Nozzles	198855	5/8 in. (16 mm) diameter
	199618	5/8 in. (16 mm) diameter, HD
	199616	3/4 in. (19 mm) diameter
	199617	3/4 in. (19 mm) diameter, HD

Date: Total Quoted Price:



## **Ordering Information**

Accessories	Stock No.	Description	Qty.	Price
Dual EZ-Change™ Low Cylinder Rack with Elevated Gun and Cable Rack	300337			
Elevated Gun and Cable Rack	300335	For use with single cylinder rack (included with dual EZ-Change low cylinder rack)		
Protective Cover	195142	Features side pocket		
Argon/Mixed Gas Regulator and Gas Hose	195050			
Full KVA Adapter Cord	300517			
Guns				
MDX™-250 MIG Gun with AccuLock™ MDX Consumables	1770035 1770036 1770037	10 ft. (3 m), 250 A, .030/.035 in. (0.8/0.9 mm) wire 12 ft. (3.7 m), 250 A, .030/.035 in. (0.8/0.9 mm) wire 15 ft. (4.6 m), 250 A, .030/.035 in. (0.8/0.9 mm) wire		
MDX™-250 MIG Gun with Industrial AccuLock™ S Consumables	1770041 1770042 1770043	10 ft. (3 m), 250 A, .035/.045 in. (0.9/1.2 mm) wire 12 ft. (3.7 m), 250 A, .035/.045 in. (0.9/1.2 mm) wire 15 ft. (4.6 m), 250 A, .035/.045 in. (0.9/1.2 mm) wire		
Spoolmatic® 15A	195156	15 ft. (4.6 m), 200 A, .023-1/16 in. (0.6-1.6 mm) for aluminum wire		
Spoolmatic® 30A	130831	30 ft. (9 m), 200 A, .023-1/16 in. (0.6-1.6 mm) for aluminum wire		
Spoolmate™ 200	300497	20 ft. (6 m), 160 A, .030–.035 in. (0.8–0.9 mm) for aluminum wire, .023–.035 in. (0.6–0.9 mm) for steel/stainless steel wires		
Optional Spoolmate™ 200 Head Tubes	300591 300592 243385	45-degree head tube 9 in. extension head tube 5 in. head tube		
XR-Aluma-Pro™ Lite Gun (air-cooled)	300948	25 ft. (7.6 m), 175 A, .030047 in. (0.8-1.2 mm) for aluminum wire		
XR-Aluma-Pro™ Gun (air-cooled)	300000 300001	15 ft. (4.6 m), 300 A, .030 – .047 in. (0.8 – 1.2 mm) for aluminum wire 25 ft. (7.6 m), 300 A, .030 – .047 in. (0.8 – 1.2 mm) for aluminum wire		

Date: Total Quoted Price:

Note: See page 7 for ordering information on the Millermatic 252 — available packages, steel and aluminum configurations, and drive roll kits/consumables.

Distributed by:

