


Dimensional Drawing



Performance Data



30PT77A

REV.
-

MOTOR PERFORMANCE

HP:	1							
Poles:	4							
No. of Speeds:	1							
Volts:	115/230	115	230					
HZ:	60	60	60					
Service Factor:	1.15							
Efficiency:	@ Rated Load	82.6	82.6					
Power Factor:	@ Rated Load	99.6	99.5					
Amps:	@ No Load							
	@ Rated Load	8.8	4.4					
	@ Service Factor	9.2	4.6					
	@ Locked Rotor	70.9	33.9					
RPM:	@ Rated Load	1725						
Ambient (°C):	40							
Altitude (FASL):								
Torques:	Breakdown	103.1	103.7					
	Locked Rotor	152.4	118.3					
	Pull-Up	137.2	106.5					
	Rated Load							
	Service Factor							
Watts:	Rated Load							
KVA Code:								
Temperature Rise:	@ Rated Load	24.6	28.3					
	@ Service Factor	29.2	33.2					
Thermal Protector:	Trip Temp (°C)							
Winding Material:	Start (Auxiliary)	Copper						
	Run (Main)	Copper						
Capacitor(s):	Start (MFD / Volts)	710 MFD / 125 VAC						
	No. of Start Capacitors							
	Run (MFD / Volts)	70 MFD / 280 VAC						
	No. of Run Capacitors							

LOW SPEED PERFORMANCE DATA:

HP:								
Poles:								
Volts:		120						
HZ:		60						
Efficiency:	@ Rated Load							
Power Factor:	@ Rated Load							
Amps:	@ No Load							
	@ Rated Load							
	@ Service Factor							
	@ Locked Rotor							
Torques:	@ Rated Load							
	Locked Rotor							
	Pull-Up							
	Rated Load							
	Service Factor							
Watts:	@ Rated Load							
Temperature Rise:	@ Rated Load							
	@ Service Factor							

DRAWING NO. PAGE 1 of 1
30PT77A

REV.
-

Dayton Electric Mfg. Co. Lake Forest, IL 60045 USA

Performance Data



30PT77A			REV. -										
Dayton Manufacturing Company													
Motor Description				Test Conditions									
Model:		T063CXCKP2072		Test Type:		Start		Run Cap:		0			
Motor ID:		1		Test Number:		40		Start Cap:		0µfd			
Poles:		4		Poles:		4		Environment:		21.4 Deg C 30 % RH 1010 hPa			
Volts:		115/208-230		Volts:		115		Tested:		11/22/2013 9:22:02 AM			
Frequency:		60		Hz:		60		Tested By:		Sharp, Gerald			
HP:		1.0		Rotation:				Gear Ratio:		1:1			
Speed:		1725		Special Cond:				Bearing Friction:		0.00 Oz-Ft			
Phase:		1		Speed Conn:				Windage Torque:		0.00 Oz-Ft			
Protector:				TestBoard:		Amps Performance		Fixture #2					
Special Points	Vline (V)	Vaux (V)	Vcap (V)	Iline (A)	Imain (A)	Iaux (A)	Watts	RPM	Tq (Oz - ft)	HP	Eff (%)	PF (%)	Cap
PUT OZ-FT	115.0	124.9	145.6	70.89	45.23	47.54	8020	10	169.6	0.020	0.2	98.4	865.9
	115.0	125.4	145.2	70.92	45.08	47.48	8035	41	170.9	0.082	0.8	98.5	867.7
	115.0	125.7	143.8	70.89	44.72	46.97	8027	154	152.4	0.279	2.6	98.5	866.5
	115.0	125.9	143.4	70.94	44.64	46.84	8035	181	155.0	0.333	3.1	98.5	866.4
	115.0	126.7	141.2	70.71	43.83	46.03	8012	317	173.1	0.653	6.1	98.5	864.8
	115.0	127.9	139.1	70.83	43.27	45.26	8023	440	183.5	0.961	8.9	98.5	862.9
	115.0	130.9	137.8	72.02	43.10	44.76	8153	556	191.5	1.267	11.6	98.4	861.8
	115.0	134.6	138.6	73.74	42.62	45.13	8368	661	192.6	1.515	13.5	98.7	864.0
	115.0	134.9	137.1	73.02	41.14	44.60	8323	759	201.2	1.818	16.3	99.1	862.8
	115.0	135.4	134.4	72.05	39.76	43.59	8226	852	208.5	2.114	19.2	99.3	860.4
	115.0	136.9	131.7	71.60	38.81	42.53	8170	938	218.6	2.442	22.3	99.2	856.6
	115.0	139.0	128.8	71.28	37.99	41.46	8129	1018	225.9	2.737	25.1	99.2	853.6
	115.0	141.6	126.0	71.13	37.28	40.52	8120	1090	232.3	3.013	27.7	99.3	853.0
	115.0	144.7	123.8	71.19	36.69	39.67	8117	1157	237.4	3.270	30.1	99.1	850.0
	115.0	148.2	121.7	71.29	36.14	38.96	8121	1220	240.5	3.492	32.1	99.0	849.0
	115.0	152.2	120.0	71.46	35.70	38.36	8136	1276	241.9	3.675	33.7	99.0	847.8
	115.0	156.4	118.8	71.65	35.36	37.89	8141	1328	239.7	3.791	34.7	98.8	846.0
	115.0	161.1	117.8	71.89	35.13	37.59	8166	1377	237.5	3.892	35.6	98.8	846.4
	115.0	166.2	117.5	72.21	35.00	37.50	8198	1420	230.2	3.891	35.4	98.7	846.3
	115.0	171.2	117.7	72.50	34.99	37.54	8219	1460	222.8	3.872	35.1	98.6	846.0
	115.0	176.5	118.5	72.81	35.03	37.84	8252	1496	214.2	3.814	34.5	98.6	847.2
	115.0	182.1	120.1	73.14	35.06	38.44	8298	1529	200.5	3.651	32.8	98.6	849.1
	115.0	187.4	122.3	73.48	35.11	39.26	8331	1559	184.4	3.422	30.6	98.6	851.2
	115.0	193.3	125.4	73.88	35.13	40.44	8390	1586	166.0	3.135	27.9	98.7	855.3
	115.0	198.7	128.4	74.18	35.18	41.67	8438	1612	152.6	2.928	25.9	98.9	860.6
	115.0	204.1	131.9	74.44	35.18	43.06	8471	1636	128.3	2.498	22.0	98.9	866.1
	115.0	209.0	135.7	74.64	35.17	44.55	8492	1658	105.0	2.072	18.2	98.9	870.9
	115.0	213.7	139.4	74.76	35.08	46.14	8516	1679	79.8	1.594	14.0	99.0	877.7
	115.0	218.3	143.1	74.76	34.94	47.83	8529	1698	53.7	1.086	9.5	99.2	886.7
	115.0	222.3	146.7	74.65	34.79	49.50	8517	1716	22.8	0.465	4.1	99.2	895.2
	115.0	225.1	149.3	74.45	34.58	50.88	8494	1731	0.0	0.000	0.0	99.2	904.0
DRAWING NO. PAGE 1 of 8												REV.	
30PT77A												-	


Dayton Electric Mfg. Co. Lake Forest, IL 60045 USA

Performance Data



30PT77A

REV.
-



Curve Descriptions:
Motor(1) Test 40 Start 115V 60 Hz 4P

- SPEED vs WATTS
- SPEED vs TORQUE
- △ SPEED vs ILine

Motor Ratings:
(1) T063CXCKP2072 ID: 1

DRAWING NO.	PAGE 2 of 8	REV.
	30PT77A	-

Dayton Electric Mfg. Co. Lake Forest, IL 60045 USA

Performance Data



30PT77A

REV.

-

Dayton Manufacturing Company

Motor Description

Model: T063CXCKP2072
Motor ID: 1
Poles: 4
Volts: 115/208-230
Frequency: 60
HP: 1.0
Speed: 1725
Phase: 1
Protector:

Test Conditions

Test Type: Run
Test Number: 42
Poles: 4
Volts: 115
Hz: 60
Rotation:
Special Cond:
Speed Conn:
TestBoard: Amtps Performance Fixture #2
Run Cap: 0
Start Cap: 0µfd
Environment: 21.4 Deg C 30 % RH 1010 hPa
Tested: 11/22/2013 9:16:55 AM
Tested By: Sharp, Gerald
Gear Ratio: 1:1
Bearing Friction: -0.16 Oz-Ft
Windage Torque: -1.44 Oz-Ft


Special Points	Vline(V)	Vaux(V)	Vcap(V)	Iline(A)	Imain(A)	Iaux(A)	Watts	RPM	Tq(Oz-ft)	HP	PF(%)	Cap
	115.0	132.5	184.9	1.95	3.32	5.073	129	1792	0.00	0.000	57.8	72.8
	115.0	129.5	175.7	4.22	2.00	4.856	442	1774	19.86	0.419	91.2	73.3
	115.0	119.9	161.2	6.96	4.38	4.421	794	1757	41.61	0.870	99.2	72.7
48.6 OZ-FT	115.0	115.4	157.0	8.03	5.68	4.294	920	1749	48.60	1.012	99.6	72.5
1 HP	115.0	115.9	157.3	7.92	5.55	4.305	909	1750	48.00	1.000	99.7	72.6
56 OZ-FT	115.0	111.8	153.0	9.27	7.10	4.189	1062	1739	56.00	1.159	99.6	72.6
	115.0	111.5	152.7	9.37	7.22	4.179	1073	1738	56.59	1.171	99.6	72.6
60.9 OZ-FT	115.0	109.6	150.4	10.11	8.08	4.107	1156	1732	60.90	1.255	99.4	72.4
1725 RPM	115.0	107.6	148.3	10.81	8.87	4.037	1233	1725	64.74	1.330	99.3	72.2
	115.0	105.0	145.6	11.70	9.89	3.956	1329	1717	69.45	1.420	98.8	72.1
	115.0	98.9	138.8	14.07	12.53	3.766	1580	1696	80.89	1.633	97.7	72.0
	115.0	92.7	133.1	16.23	14.99	3.606	1794	1674	86.55	1.725	96.1	71.8
	115.0	86.8	127.9	18.37	17.41	3.469	1997	1648	94.81	1.861	94.5	72.0
	115.0	81.2	123.3	20.50	19.82	3.346	2186	1622	97.44	1.882	92.7	72.0
	115.0	75.9	119.4	22.44	22.00	3.248	2347	1595	102.24	1.941	90.9	72.2
	115.0	70.4	116.0	24.44	24.18	3.167	2496	1563	100.32	1.867	88.8	72.4
BDT OZ-FT	115.0	68.5	114.9	25.18	25.00	3.136	2550	1551	103.12	1.904	88.1	72.4
	115.0	65.3	113.1	26.30	26.26	3.088	2631	1530	99.21	1.808	87.0	72.4
	115.0	60.5	111.2	28.00	28.17	3.041	2740	1495	98.33	1.750	85.1	72.6
	115.0	55.8	109.7	29.62	29.99	3.010	2835	1457	94.74	1.643	83.3	72.8
	115.0	51.2	108.7	31.18	31.74	2.990	2918	1414	90.80	1.529	81.4	72.9
	115.0	47.0	108.2	32.59	33.33	2.983	2986	1369	86.65	1.412	79.7	73.1
	115.0	43.1	108.0	33.93	34.84	2.984	3044	1320	80.58	1.266	78.0	73.3
	115.0	39.2	108.2	35.16	36.24	2.993	3086	1266	74.40	1.121	76.3	73.4
	115.0	35.6	108.7	36.30	37.52	3.007	3119	1208	67.64	0.972	74.7	73.4
	115.0	32.4	109.4	37.32	38.68	3.031	3145	1145	60.76	0.828	73.3	73.5
	115.0	29.4	110.3	38.25	39.74	3.053	3160	1077	53.41	0.685	71.8	73.5
	115.0	26.9	111.4	39.08	40.69	3.090	3171	1004	46.35	0.554	70.5	73.6
	115.0	24.3	112.3	39.83	41.56	3.116	3174	926	38.50	0.424	69.3	73.6
	115.0	22.1	113.3	40.51	42.32	3.143	3171	841	30.78	0.308	68.1	73.6
	115.0	19.6	113.9	41.09	43.00	3.147	3162	750	21.91	0.196	66.9	73.3
	115.0	15.8	113.7	41.49	43.50	3.114	3129	653	12.48	0.097	65.6	72.7
	115.0	12.0	116.4	41.43	43.57	3.163	3104	550	11.86	0.078	65.2	72.1
	115.0	14.5	120.1	41.80	44.00	3.289	3139	441	9.37	0.049	65.3	72.6
	115.0	14.3	120.7	41.97	44.20	3.286	3138	322	9.64	0.037	65.0	72.2
	115.0	16.0	122.8	42.24	44.54	3.397	3149	197	2.11	0.005	64.8	73.4
	115.0	16.8	124.7	42.17	44.56	3.477	3150	64	10.49	0.008	64.9	74.0

Performance Data



30PT77A

REV.
-



Curve Descriptions:
Motor(1) Test 42 Run 115V 60 Hz 4P

- SPEED vs WATTS
- SPEED vs TORQUE
- △ SPEED vs ILine

Motor Ratings:
(1) T063CXCKP2072 ID: 1

Performance Data



30PT77A

REV.

-

Dayton Manufacturing Company

Motor Description

Model: T063CXCKP2072
Motor ID: 1
Poles: 4
Volts: 115/208-230
Frequency: 60
HP: 1.0
Speed: 1725
Phase: 1
Protector:

Test Conditions

Test Type: Start
Test Number: 6
Poles: 4
Volts: 230
Hz: 60
Rotation:
Special Cond:
Speed Conn:
TestBoard: Amtps Performance Fixture #2
Run Cap: 0
Start Cap: 0µfd
Environment: 22.0 Deg C 42 % RH 998 hPa
Tested: 11/21/2013 3:01:48 PM
Tested By: Sharp, Gerald
Gear Ratio: 1:1
Bearing Friction: -0.32 Oz-Ft
Windage Torque: -1.28 Oz-Ft


Special Points	Vline (V)	Vaux (V)	Vcap (V)	Iline (A)	Imain (A)	Iaux (A)	Watts	RPM	Tq (Oz-ft)	HP	Eff (%)	PF (%)	Cap
	230.0	204.6	123.6	34.02	25.16	39.47	7480	8	129.64	0.013	0.1	95.6	846.8
	230.0	204.6	123.3	33.98	25.04	39.33	7460	41	137.69	0.067	0.7	95.4	846.3
PUT OZ-FT	230.0	206.2	121.6	33.89	24.47	38.81	7448	166	118.26	0.234	2.3	95.5	846.5
	230.0	206.4	121.5	33.90	24.38	38.73	7449	180	119.69	0.257	2.6	95.5	845.8
	230.0	208.5	119.7	33.85	23.43	38.14	7452	316	137.48	0.517	5.2	95.7	845.3
	230.0	210.5	117.7	33.79	22.54	37.39	7428	439	144.08	0.754	7.6	95.6	842.9
	230.0	213.9	115.9	34.07	21.42	36.75	7487	556	152.02	1.006	10.0	95.5	840.8
	230.0	217.8	116.0	34.69	20.15	36.82	7654	662	154.37	1.217	11.9	95.9	842.3
	230.0	218.7	115.0	34.39	18.99	36.45	7628	761	159.69	1.447	14.1	96.4	841.1
	230.0	220.8	112.7	34.10	17.74	35.62	7569	852	169.37	1.718	16.9	96.5	838.4
	230.0	223.9	110.1	33.82	16.43	34.76	7525	938	177.88	1.986	19.7	96.7	837.4
	230.0	227.2	107.6	33.59	15.03	33.90	7480	1017	183.14	2.216	22.1	96.8	835.6
	230.0	230.6	105.3	33.42	13.55	33.09	7440	1090	191.39	2.484	24.9	96.8	833.3
	230.0	234.6	103.1	33.28	12.00	32.35	7410	1158	194.35	2.679	27.0	96.8	832.2
	230.0	238.6	101.2	33.14	10.41	31.69	7380	1219	196.09	2.846	28.8	96.8	830.9
	230.0	243.0	99.4	33.02	8.77	31.10	7347	1277	197.65	3.004	30.5	96.7	830.1
	230.0	247.7	98.1	32.90	7.13	30.64	7327	1328	196.87	3.113	31.7	96.8	828.9
	230.0	252.5	96.9	32.79	5.52	30.30	7302	1377	193.82	3.176	32.4	96.8	829.0
	230.0	257.3	96.3	32.67	4.04	30.08	7269	1420	190.29	3.217	33.0	96.7	828.7
	230.0	262.3	96.1	32.56	2.90	30.00	7242	1460	187.53	3.260	33.6	96.7	828.5
	230.0	267.4	96.4	32.45	2.68	30.12	7217	1497	179.33	3.196	33.0	96.7	828.6
	230.0	272.4	97.7	32.36	3.48	30.52	7203	1530	172.12	3.136	32.5	96.8	829.0
	230.0	277.4	99.2	32.29	4.83	31.07	7195	1561	160.42	2.981	30.9	96.9	830.8
	230.0	282.4	101.4	32.20	6.36	31.85	7186	1589	144.05	2.725	28.3	97.0	833.3
	230.0	287.5	104.3	32.14	8.03	32.81	7184	1615	128.73	2.475	25.7	97.2	834.8
	230.0	292.3	107.0	32.05	9.62	33.81	7178	1638	117.15	2.285	23.7	97.4	838.4
	230.0	296.7	110.2	31.95	11.25	34.95	7163	1660	94.62	1.870	19.5	97.5	841.5
	230.0	301.4	113.6	31.83	12.93	36.26	7151	1682	78.60	1.573	16.4	97.7	846.4
	230.0	305.4	117.1	31.70	14.49	37.56	7123	1700	55.96	1.133	11.9	97.7	850.9
	230.0	309.6	121.2	31.54	16.23	39.10	7103	1720	31.57	0.647	6.8	97.9	855.5
	230.0	313.3	124.9	31.35	17.86	40.59	7063	1738	8.48	0.175	1.9	97.9	861.8
	230.0	314.5	126.2	31.26	18.51	41.21	7047	1745	0.00	0.000	0.0	98.0	866.4

Performance Data



30PT77A

REV.
-



Performance Data




30PT77A		REV.
		-

Dayton Manufacturing Company													
Motor Description				Test Conditions									
Model:	T063CXCKP2072			Test Type:	Run			Run Cap:	0				
Motor ID:	1			Test Number:	7			Start Cap:	0µfd				
Poles:	4			Poles:	4			Environment:	22.0 Deg C 42 % RH 998 hPa				
Volts:	115/208-230			Volts:	230			Tested:	11/21/2013 2:31:11 PM				
Frequency:	60			Hz:	60			Tested By:	Sharp, Gerald				
HP:	1.0			Rotation:				Gear Ratio:	1:1				
Speed:	1725			Special Cond:				Bearing Friction:	0.00 Oz-Ft				
Phase:	1			Speed Conn:				Windage Torque:	-1.60 Oz-Ft				
Protector:				TestBoard:	Amps Performance			Fixture #2					

Special Points	Vline(V)	Vaux(V)	Vcap(V)	Iline(A)	Imain(A)	Iaux(A)	Watts	RPM	Tq(Oz- ft)	HP	PF (%)	Cap
	230.0	167.4	185.0	1.04	4.10	5.062	152	1794	0.00	0.000	63.7	72.6
	230.0	172.4	175.0	2.19	2.97	4.812	464	1775	20.39	0.431	92.2	72.9
	230.0	172.0	160.5	3.57	2.66	4.390	814	1757	42.14	0.881	99.1	72.5
1 HP	230.0	170.3	156.8	4.02	2.95	4.286	919	1750	48.00	1.000	99.5	72.5
48.6 OZ-FT	230.0	170.2	156.5	4.07	2.99	4.277	930	1749	48.60	1.012	99.5	72.5
56 OZ-FT	230.0	168.4	152.6	4.70	3.54	4.163	1073	1739	56.00	1.160	99.3	72.4
	230.0	168.2	152.3	4.75	3.58	4.153	1084	1739	56.54	1.171	99.2	72.3
60.9 OZ-FT	230.0	167.8	150.0	5.11	3.93	4.084	1167	1732	60.90	1.255	99.3	72.2
1725 RPM	230.0	167.2	147.5	5.50	4.32	4.010	1255	1725	65.20	1.339	99.2	72.1
	230.0	166.1	145.1	5.93	4.77	3.930	1344	1718	69.73	1.426	98.5	71.9
	230.0	163.9	138.4	7.05	6.01	3.747	1581	1696	80.75	1.631	97.5	71.8
	230.0	161.2	132.7	8.16	7.31	3.584	1799	1674	87.37	1.741	95.9	71.7
	230.0	158.8	127.4	9.26	8.63	3.445	2007	1649	95.10	1.867	94.2	71.7
	230.0	156.2	122.9	10.30	9.89	3.332	2191	1623	97.85	1.891	92.5	71.9
	230.0	153.5	119.1	11.29	11.09	3.237	2354	1595	102.61	1.948	90.7	72.1
	230.0	150.6	115.8	12.30	12.30	3.161	2511	1564	101.08	1.882	88.8	72.4
BDT OZ-FT	230.0	149.5	114.8	12.66	12.75	3.134	2562	1552	103.74	1.916	88.0	72.5
	230.0	147.8	113.3	13.21	13.42	3.099	2640	1531	99.94	1.822	86.9	72.6
	230.0	144.8	111.4	14.08	14.50	3.058	2751	1496	98.81	1.759	84.9	72.8
	230.0	141.9	110.1	14.90	15.51	3.028	2843	1458	95.59	1.659	83.0	72.9
	230.0	139.1	109.3	15.68	16.48	3.017	2929	1414	91.30	1.537	81.2	73.2
	230.0	136.1	109.1	16.40	17.38	3.014	2992	1369	87.32	1.423	79.3	73.3
	230.0	133.5	109.2	17.06	18.20	3.022	3047	1320	81.02	1.273	77.7	73.4
	230.0	130.6	109.6	17.67	18.98	3.036	3086	1267	74.97	1.130	75.9	73.5
	230.0	128.0	110.3	18.24	19.70	3.059	3119	1208	68.27	0.982	74.3	73.5
	230.0	125.7	111.3	18.76	20.35	3.092	3144	1145	61.33	0.836	72.9	73.7
	230.0	123.1	112.5	19.22	20.95	3.124	3155	1077	53.97	0.692	71.4	73.7
	230.0	120.7	113.8	19.64	21.49	3.160	3164	1004	46.75	0.559	70.0	73.7
	230.0	118.5	114.9	20.01	21.97	3.191	3163	926	39.15	0.432	68.7	73.7
	230.0	116.7	116.1	20.35	22.40	3.222	3159	841	31.09	0.311	67.5	73.6
	230.0	115.0	116.9	20.63	22.79	3.231	3146	750	22.37	0.200	66.3	73.3
	230.0	113.7	116.9	20.83	23.08	3.204	3113	653	12.79	0.099	65.0	72.7
	230.0	110.2	119.7	20.81	23.18	3.266	3087	550	12.33	0.081	64.5	72.4
	230.0	106.7	123.6	21.00	23.44	3.392	3123	440	9.61	0.050	64.7	72.8
	230.0	106.0	124.2	21.08	23.55	3.390	3121	322	10.26	0.039	64.4	72.4
	230.0	104.3	126.3	21.21	23.76	3.498	3132	196	0.46	0.001	64.2	73.4
	230.0	102.1	128.3	21.18	23.80	3.583	3129	64	11.81	0.009	64.3	74.1


DRAWING NO.	PAGE 7 of 8	REV.
30PT77A		-

Performance Data



Dayton Electric Mfg. Co. Lake Forest, IL 60045 USA

Wiring Diagram



Dayton Electric Mfg. Co. Lake Forest, IL 60045 USA

Dayton[®]**INDUSTRIAL MOTOR**Part
No

30PT77A

**HP:** 1.0**PH:** 1**VOLTS:** 115/230**HZ:** 60**AMPS:** 8.8/4.4**FR:** 56**RPM:** 1725**INS CL:** B**DUTY:** CONT**AMB:** 40 °C**SF:** 1.15**SFA:** 9.2/4.6**KVA CODE:** J**ENCL:** ODP**THERMALLY PROTECTED:** AUTOMFG. NO. PROT. CODE : 00440 AVG. F.L. 82.6
EFF.**MTR REF:** T63CXCKP-2072**USABLE FOR 208 V AT 1.0 SF**


E37403




258501

NEMA
Premium[™]**Disconnect Power Before Making Any
Electrical Connections or Changes****CONNECTIONS**

115 VOLT



230 VOLT

**MOTOR IS CW ROTATION SHAFT END
TO REVERSE ROTATION INTERCHANGE
RED AND BLACK LEADS.****Mfd for Dayton Electric Mfg. Co., Lake Forest, IL 60045 USA****Made in Mexico**