Straight Blade Devices

20A, 125V, 2 Pole, 3 Wire Grounding

HBL®Extra Heavy Duty MAX Hospital Grade **Duplex Receptacle**

HUBBELL

Features

- Slender/compact design
- Impact-resistant finder groove face
- Triple wipe contacts
- Entire face illuminated by two LEDs

Ordering Information

Description **Device Color UPC Number Catalog Number** HBL8300ILGY Illuminated face, back and 783585016481 Grav side wired.

Listings

UL Listed to UL498 File No. E2186 **CSA Certified** Fed. Spec. W-C-596 NEMA® WD-6 Compliant

Specifications

Face Polycarbonate

Base

By-Pass Power Contacts .036". (.9) Nickel plated brass

.031 in. (.8) Brass **Ground Contacts** Clamp Nickel plated steel

Terminal Screws Brass Mounting Strap

Automatic Self-grounding Clip .050 in. (1.3) Nickel plated brass

Mounting Screws Stainless Steel

Performance

Dielectric Voltage

Electrical

Current Interrupting Certified for current interrupting at full rated

current

Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device Terminal Accommodation #12-#10 AWG stranded or solid copper wire only Terminals identified in accordance with UL 498 **Terminal Identification**


and CSA

Environmental

Flammability UL 94V-2

Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o





Complementary Products

Wallplate or Weatherproof Cover **Duplex Opening**

Online Resources

Customer Sales Drawings eCatalog

Installation Instructions

