



## R-266

Insulated impact glove with waterproof barrier and grip system.



Impact



Cold

Abrasion Protection



Cut



Heavy Duty

## Hands stay warm and dry with heavy winter-time impact protection and synthetic grip patches.

The Ringers® 266 Heavy Duty Impact glove combines insulation and a waterproof barrier with a synthetic leather palm and grip patch system, providing 'go-anywhere' protection against impact hazards and the elements.

- Developed with Ringers' F3 Technology™ and patented TPR design for superior dexterity and comfort.
- Touchscreen compatible index, middle and thumb tips lessen the need to remove gloves, while high visibility increases safety.



### Industries

- Mining
- Oil and gas

### Applications

- Engagement and release of drill string slips
- Chaining up pipes
- Installation and dismantling of rigs
- Assembly and disassembly of large pipes
- Unloading and stacking pipe
- Preparation of site - unloading of lines and valves
- Set-up of pressure manifold and tubing injector head
- General pumping work
- Preparation of site - set-up and disassembly of tool string
- Handling iron - rigging work
- Handling of tools
- Environmental clean-up and remediation
- Handling iron
- Valve - line maintenance and repair
- Heavy machine operation
- Equipment maintenance and repair
- Pipe handling



## R-266


Insulated impact glove with waterproof barrier and grip system.

### Key Features

- TPR impact protection on top of hand and full length of fingers
- Synthetic leather grip patch system on palm
- 100 gram Thinsulate™ insulation for additional warmth
- Proprietary waterproof barrier to keep hands dry
- Touchscreen compatible index, middle and thumb tips
- Extended neoprene wrist closure with TPR pull tab
- Kevlar® stitched palm
- High visibility for increased safety

### Performance Standards & Regulatory Compliance

#### REACH Compliant



### Specifications

| BRAND   STYLE | DESCRIPTION   | Gauge | SIZE                 | COLOR  | PACKAGE                        |
|---------------|---|-------|----------------------|--------|--------------------------------|
| RINGERS® R266 | <b>Liner Material:</b> Polyester<br><b>Cuff Style:</b> Extended |       | 8, 9, 10, 11, 12, 13 | Hi Viz | 5 pairs/bag,<br>10 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2022 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

