



products meet or exceed applicable ANSI/BIFMA standards

MODEL 9108-B SHOWN



300lb. weight capacity!

SPECS:

- Features a Sturdy 3/4" square frame 19-gauge steel tubing with non-marring plastic glides
- Steel Standard: ASTM A513
- Foam Standard: 1.8lb. density, 46 ILD
- Seat is cushioned with 1 1/2" of high-density Grade A foam
- Vinyl & Foam are Cal-117 rated
- Available with thick .80MM vinyl
- Tapered back has built-in handhold
- Eight plastic stack bumpers protect the powder-coated frame finish
- Plywood core seat and back
- Stack 8-10 high with DY81 or DY9000 dollies


DIMENSIONS:

OVERALL: 33"H X 16"W X 15 3/4"D


SEAT: 18"H X 15 3/4"W X 15"D

CAL-117 RATED

VINYL UPHOLSTERY



CHAIR FRAMES



AVAILABLE ACCESSORIES



USE WITH:



Model #DY9000
Stacking Chair Dolly

Model #DY81
Stacking Chair Dolly

National Public Seating

