## Twist-Lock® Devices 15A, 125V, 2 Pole, 3 Wire Grounding Stainless Steel Flanged Receptacle

### Features

- Heat resistant thermoset construction
- Stainless steel casing
- #8-32 terminal screws
- Mounting screws included

### **Ordering Information**

Description Device Color Stainless steel casing, Brown/Stainless brown phenolic

UPC Catalog Number 783585236766 HBL4715

### Listings

Listed to UL 498 Fed. Spec. W-C-596 Certified to CSA C22.2 No.42

# HUBBELL



HBL4720C

### Accessories

Plug

### Resources

eCatalog

### **Specifications**

Flange	Stainless steel
Blades	Brass
Terminal Screws	Brass
Mounting Screw	Nickel plated brass

### Performance

Electrical Current Interrupting Dielectric Voltage	Certified for current interrupting at full rated current Withstands 2,000V minimum
Mechanical Terminal Accommodation	#18 AWG - #10 AWG solid or stranded copper wire only.
Terminal Identification	Terminals identified in accordance with UL 498
Environmental Flammability Moisture Resistance Operating Temperatures	HB or better per UL94/CSA 22.2 No.0.17 IP20 Suitability Maximum Continuous 75°C; Minimum -40°C (w/o impact)

