



**MCR
SAFETY**

9178NF

Memphis

Cut Protection Specification Sheet

PRODUCT DESCRIPTION:

Kevlar® gloves are used for general purpose work applications to provide cut and abrasion resistance, using high performance yarns, to further protect the hands when working with sharp objects. Black color hides dirt and grime so gloves look better longer while offering the same great performance as yellow Kevlar®. Gloves with a polymer coating offer better grip and durability for those tough jobs. The 9178NF features a 13 Gauge black Kevlar® / Synthetic shell with a black nitrile foam coating on the palm and fingertips.

FEATURES:

- Kevlar® will not melt, ignite or conduct electricity
- High comfort level, Allows manual dexterity
- Certified by DuPont™ as a licensed glove manufacturer
- Nitrile foam coating

APPLICATIONS:

Automotive Assembly, Bottling, Canning, Glass handling, HVAC, Manufacturing, Sheet metal industry



TECHNICAL DATA FOR: 9178NF

Series	Memphis	EN 388 : CE Score - Abrasion	4
Material Group	Strings	EN 388 : CE Score - Cut	5
Product Type	Cut Protection	EN 388 : CE Score - Tear	4
Glove Size	Large	EN 388 : CE Score - Puncture	2
Gauge	13 Gauge		
Material	Kevlar		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

9178NF

Memphis

Cut Protection Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
9178NFL	Large	12.75	4.68	2.83	29.664 lb.	0.206
9178NFM	Medium	12.41	4.48	2.68	26.784 lb.	0.186
9178NFS	Small	12.25	4.24	2.68	50.112 lb.	0.348
9178NFXL	X - Large	13.18	5.00	2.87	31.392 lb.	0.218
9178NFXS	X - Small	0	0	N/A	24.336 lb.	0.169
9178NFXXL	XX - Large	13.30	5.16	2.91	32.400 lb.	0.225
9178NFXXXL	XXX - Large	0	0	N/A	33.264 lb.	0.231

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved