

Integrated LED Tubes

T5 Glass Tubes



Project Name _____

Date _____ Type _____

Notes _____

Convert your existing linear fluorescent fixture to LED lighting without needing a comprehensive reinstall. LED tubes are ideal for those seeking high energy savings with minimal installation time. Each LED tube is operated by an internal Current Lightech™ driver. Current integrated LED tubes run on electronic instant-start or programmed start ballasts.

PERFORMANCE HIGHLIGHTS:

T5 Glass Tubes	
Light Output Range:	1000-3900 Lumens
CRI:	80+
CCT:	3000K, 3500K, 4000K & 5000K
Wattage:	7W-25.5W
Life:	50,000 hours L70
Temperature Rating:	-20°C to 40°C
Rating:	Damp
Fixtures:	Open or Enclosed
Dimming:	Dimmable with compatible dimming ballasts
Ballast Compatability Guide:	gecurrent.com/LEDTUBES-ballastcompatibility
Certification:	DLC Listed

BENEFITS:

- Fast and Easy LED upgrade
- Low energy LFL replacement
- 66% longer life than LFL (50,000 vs. 30,000 hours)
- Better quality of light –instant on
- Fully illuminates fixture - 270° light distribution
- Easy disposal, non-hazardous waste

LEARN MORE:

To learn more about saving money and energy, go to www.gecurrent.com.

Information provided is subject to change without notice. Please verify all details with Current. All values are design or typical values when measured under laboratory conditions, and Current makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

LIMITED WARRANTY

5 Years



Integrated LED Tubes

T5 Glass Tubes

Spec Table

Project Name _____

Date _____ Type _____

Notes _____

Base Type	Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	DLC®	UL	# Location Rating	Additional Information
Integrated 4 ft LED Glass T5 HO Tubes (Operates on Instant Start or Program Start Ballast)																
T5	G5	25.5	19203	LED26ET5/G/4/830		20	46	3650	3000K	80+		50,000	Yes	Yes	Damp	Requires T5 HO Ballast
	G5	25.5	19221	LED26ET5/G/4/835		20	46	3750	3500K	80+		50,000	Yes	Yes	Damp	Requires T5 HO Ballast
	G5	25.5	19227	LED26ET5/G/4/840		20	46	3800	4000K	80+		50,000	Yes	Yes	Damp	Requires T5 HO Ballast
	G5	25.5	19348	LED26ET5/G/4/850		20	46	3900	5000K	80+		50,000	Yes	Yes	Damp	Requires T5 HO Ballast
	G5	25.5	19488	LED26ET5/G/4/865		20	46	3800	6500K	80+		50,000	-	Yes	Damp	Requires T5 HO Ballast
Integrated 2 ft LED Glass T5 HO Tubes (Operates on Instant Start or Program Start Ballast)																
T5	G5	11	34413	LED11ET5/G/2/830		20	22	1500	3000K	80+		50,000	-	Yes	Damp	Requires T5 HO Ballast
	G5	11	34417	LED11ET5/G/2/835		20	22	1550	3500K	80+		50,000	-	Yes	Damp	Requires T5 HO Ballast
	G5	11	34418	LED11ET5/G/2/840		20	22	1600	4000K	80+		50,000	-	Yes	Damp	Requires T5 HO Ballast
	G5	11	34424	LED11ET5/G/2/850		20	22	1600	5000K	80+		50,000	-	Yes	Damp	Requires T5 HO Ballast
Integrated 4 ft LED Glass T5 HE Tubes (Operates on Instant Start or Program Start Ballast)																
T5	G5	13	34351	LED13ET5G4/830HE		20	46	1900	3000K	80+		50,000	Yes	Yes	Damp	Requires T5 HE Ballast
	G5	13	34354	LED13ET5G4/835HE		20	46	1950	3500K	80+		50,000	Yes	Yes	Damp	Requires T5 HE Ballast
	G5	13	34355	LED13ET5G4/840HE		20	46	2000	4000K	80+		50,000	Yes	Yes	Damp	Requires T5 HE Ballast
	G5	13	34367	LED13ET5G4/850HE		20	46	2000	5000K	80+		50,000	Yes	Yes	Damp	Requires T5 HE Ballast
Integrated 3 ft LED Glass T5 HE Tubes (Operates on Instant Start or Program Start Ballast)																
T5	G5	10	34371	LED10ET5G3/830HE		20	34	1500	3000K	80+		50,000	-	Yes	Damp	Requires T5 HE Ballast
	G5	10	34376	LED10ET5G3/835HE		20	34	1550	3500K	80+		50,000	-	Yes	Damp	Requires T5 HE Ballast
	G5	10	34401	LED10ET5G3/840HE		20	34	1600	4000K	80+		50,000	-	Yes	Damp	Requires T5 HE Ballast
	G5	10	34402	LED10ET5G3/850HE		20	34	1600	5000K	80+		50,000	-	Yes	Damp	Requires T5 HE Ballast
Integrated 2 ft LED Glass T5 HE Tubes (Operates on Instant Start or Program Start Ballast)																
T5	G5	7	34403	LED7ET5/G2/830HE		20	22	1000	3000K	80+		50,000	-	Yes	Damp	Requires T5 HE Ballast
	G5	7	34404	LED7ET5/G2/835HE		20	22	1100	3500K	80+		50,000	-	Yes	Damp	Requires T5 HE Ballast
	G5	7	34411	LED7ET5/G2/840HE		20	22	1150	4000K	80+		50,000	-	Yes	Damp	Requires T5 HE Ballast
	G5	7	34412	LED7ET5/G2/850HE		20	22	1150	5000K	80+		50,000	-	Yes	Damp	Requires T5 HE Ballast

Information provided is subject to change without notice. Please verify all details with Current. All values are design or typical values when measured under laboratory conditions, and Current makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

UL 1993 Environmental Requirements for LED LAMPS

Location, damp – Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry – Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet – Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.