

Features and Benefits

Commercial Tamper-Resistant GFCI Receptacles

- Patented shutter design for tamper-resistant protection
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology includes disconnecting power to the receptacle if critical components are damaged and GFCI protection is lost
- Alarm version provides audible notification of a trip condition



GFTRST83B



Hospital Grade Tamper-Resistant GFCI Receptacles



15A 125V
NEMA 5-15R
UL CSA
0.5 HP



20A 125V
NEMA 5-20R
UL CSA
1 HP

Description	Rating	Color	Catalog Number	
Night Light	15 and 20A	Black	GFTRST82BKNL	GFTRST83BKNL
Two LED Night Lights,	125V AC	Brown	GFTRST82NL	GFTRST83NL
Flush, nylon face,		Gray	GFTRST82GYNL	GFTRST83GYNL
back and side wired,		Ivory	GFTRST82INL	GFTRST83INL
multiple drive screws,		Light Almond	GFTRST82LANL	GFTRST83LANL
self-grounding staple.		Red	GFTRST82RNL	GFTRST83RNL
		White	GFTRST82WNL	GFTRST83WNL
Alarm,	15 and 20A	Black	GFTRST82BKB	GFTRST83BKB
Flush, nylon face,	125V AC	Brown	GFTRST82B	GFTRST83B
back and side wired,		Gray	GFTRST82GYB	GFTRST83GYB
multiple drive screws,		Ivory	GFTRST82IB	GFTRST83IB
self-grounding staple.		Light Almond	GFTRST82LAB	GFTRST83LAB
		Red	GFTRST82RB	GFTRST83RB
		White	GFTRST82WB	GFTRST83WB



GFTRST83WNL



GFTRST83GYB

Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles are furnished with a matching color thermoplastic wallplate, 20 amp feed-through capability. See page Tech-10 for Tamper-Resistant description.

Product Dimensions

GFCI Receptacle	
A	3.27 (83.1)
B	2.75 (69.8)
C	1.75 (44.5)
D	1.47 (37.4)
E	1.10 (27.9)

