

SHOWA

S-TEX 377

Innovative cut performance glove combining high cut resistance S-TEX® liner using Hagane Coil™ technology and a double nitrile and foamed nitrile coating for optimal long lasting grip.

FEATURES

- Engineered Hagane Coil® technology
- EN388:2016 Cut resistance level 4 / D (19Newton)
- Double-dipped, fully coated, with an extra foamed nitrile finish on palm
- 13 Gauge knitted liner
- Anatomical hand shape design
- Seamless knit
- Nitrile foam grip

BENEFITS

- Excellent cut resistance performance: D/19 Newton
- Nitrile coating with a second foamed nitrile coating providing high abrasion resistance EN388: 4
- Protects the hand from oils, hydrocarbons, grease and abrasion, with long lasting grip performance under wet and oily conditions
- An ergonomically designed hand mould replicates the natural curvature of the human hand and thus reduces hand fatigue, increasing productivity and dexterity
- Seamless knitting gives no irritation
- Liquid-proof to end of coated area
- Optimal grip performance in wet & oily conditions

INDUSTRY



Aerospace



Agriculture



Construction



Engineering



Glass



Manufacturing



Mechanical

IDEAL APPLICATIONS

- Light assembly of oil-coated pieces
- Steel fabrication
- Assembly dry and oily parts
- Handling glass and windows
- Bottling
- Canning
- HVAC
- Mounting and dismantling



MATERIAL

- Nylon
- Polyester
- Seamless knit

COATING

- Foam nitrile
- Nitrile

GRIP

- Foam

STANDARDS



0120

ANSI / ISEA
105-2016



EN 388:2016



4121X

SHOWA

S-TEX 377



PACKAGING

- 12 Pair per polybag
- 6 Polybags per case
- 72 Pair per case



SIZES

- S
- M
- L
- XL
- XXL



COLOUR

- Gray/ blue coating & black palm



[YOU MIGHT ALSO BE INTERESTED IN

SHOWA
377



MATERIAL
Polyester
COATING
Foam nitrile

SHOWA
377-IP



MATERIAL
Nylon
COATING
Foam nitrile

SHOWA
S-TEX 376



MATERIAL
Polyester
COATING
Foam nitrile

SHOWA
234



MATERIAL
HPPE
COATING
Nitrile

[USER INSTRUCTIONS

Do not use where there are chemical, electrical, thermal or entanglement risks. Wash at 40°C max. Performance levels as per standard EN388 retained after 3 washes, subject to variations linked to actual usage conditions. The performance levels apply to the coated surface only. Store in a dry place, away from the light. Do not use where there are electrical, thermal or entanglement risks. Discard used gloves in compliance with local regulations. Permeation information does not reflect the actual duration of protection in the workplace due to other factors that may influence the performance. Store in a dry place, away from the light.

[DISCLAIMER

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

Get in touch

SHOWA USA | 579 Edison Street - Menlo, GA 30731, USA

USA@SHOWAGroup.com

© SHOWA Group 2018 | All rights reserved