



Pro-Wipe[®] AP

All-Purpose Low Linting Wiper 50% Rayon/50% Polyester

Pro-Wipe[®] AP is an all purpose industrial rayon/polyester nonwoven wiper. Durable and low-linting, Pro-Wipe[®] AP is tough enough to be a rag replacement and clean enough to be used in a controlled manufacturing environment.



Key Attributes

- 50% Rayon 50% Polyester
- No binders or other chemical additives
- Smooth and soft with high strength and durability
- Highly absorbent core due to inner layer of cellulose

Benefits

- Chemically compatible with common cleaning and disinfecting solutions
- Low linting and abrasion resistant
- Autoclavable
- Absorbs water and oil based solutions

Applications

- Spill pick up
- General cleaning of manufacturing equipment and bench top surfaces
- Cleaning of lab equipment
- Surface prep

Technical Data:

Attribute		Units	Value	Test Method
Basis Weight		g/m ²	62.9	TAPPI T410
Fibers	≥ 100µm	fibers/cm ²	33	IEST-RP-CC004.3, Sec 6.1.3 / Sec 6.2.2
Water Absorbency		%	700	IEST-RP-CC004.3, Sec 8.1 modified
Extractable Matter	DI water	%	0.041	IEST-RP-CC004.3, Sec 7.1.2
	IPA	%	0.0032	
Tensile Strength	MD	lb/in	13	ASTM D5035
	CD	lb/in	4.0	

Technical data represented in this table are typical values at the time of publication. These should not be used as product specifications.

Cloth-like Feel



Pro-Wipe[®] AP is available in the following configurations:

Can be used with Center-Pull Towel Dispensers



Flat Pack



Quarter-Folded



Perforated Roll

Pro-Wipe[®] Family

Pro-Wipe[®] AP
Pro-Wipe[®] OS
Pro-Wipe[®] SE Knit

Order Information:

Product	Number	Size	Shts/pk	Pks/cs	Style
Pro-Wipe [®] AP	PWAP09.24	9x9" (23x23cm)	150	24	Flat Pack
Pro-Wipe [®] AP	PWAP12.24	12x12" (30x30cm)	100	24	Flat Pack
Pro-Wipe [®] AP	PWAP.12130F.20	12x13" (30x33cm)	50	20	Quarter Folded
Pro-Wipe [®] AP	PWAP.PR0915.4	9x15" (23x38cm)	250	4	Perforated Roll