



**MCR
SAFETY**

6521SCO

**Supported / Dipped gloves
Specification Sheet**

PRODUCT DESCRIPTION:

Frigid frozen fingers? No frickin' way, These foam-insulated gloves keep hands warm and dry. They are resistant to abrasions, oil, acids, chemicals and caustics.

FEATURES:

- Orange Double Dipped
- Foamed Lined
- Sandy Finish
- Safety Cuff

APPLICATIONS:

Food, Cold storage applications, Fisheries, Transportation, Warehousing



TECHNICAL DATA FOR: 6521SCO

Material Group	Supported
Product Type	Supported / Dipped gloves
Glove Size	Large
Material	PVC
Grade	Industrial Grade
Insulated	Insulated
Lining	Foam
Thumb Style	Wing


HI VIS	High Visibility
Overall Length	12 in.
ANSI Abrasion	ANSI Abrasion 3



MCR
SAFETY

6521SCO

Supported / Dipped gloves
Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
6521SCO	Large	12.640	6.09	2.640	38.718 lb.	6.453

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved