





REVISION		
REV	DATE	DESCRIPTION
A	4/6/2011	501967ERP - RELEASE MRY
B	1/23/18	518779ECP/D - ADD WIDTH, HEIGHT AND LENGTH TOLERANCE MRY
C	2/27/19	520462ECP/D - UPDATE WIDTH, HEIGHT, LENGTH DIMS & TOLERANCE MRY
D	3/5/19	520513ECP/D - UPDATE HEIGHT TOLERANCE MRY
E	3/7/19	520532ECP/D - UPDATE LENGTH TOLERANCE MRY
F	3/8/19	520534ECP/D - UPDATE HEIGHT TOLERANCE MRY



SPECIFICATIONS:

VOLTAGE RATING: 600V

AMPERE RATING: 30 AMPERES

INTERRUPT RATING: 100kA

TERMINAL TYPE: PRESSURE PLATE/ QUICK CONNECT

SUGGESTED TORQUE: 2.3 N-m (20 IN-LBS)

WIRE RANGE: 10-14 AWG Cu ONLY
SOLID/STRANDED

APPROVALS: UL RECOGNIZED (FILE NO. E14721)
CSA CERTIFIED (FILE NO. LR7316)

●	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
(ST)	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

MATL SPEC	FINISH		
DRW MYORK	DATE 3/25/2011	SCALE NTS	FINISH GOOD WT GRAMS/PIECE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

3RD ANGLE PROJECTION	
----------------------	--

TITLE L60030M-PQ SERIES OUTLINE