



**MCR
SAFETY**

CP25 MCR Guard Unsupported Specification Sheet

PRODUCT DESCRIPTION:

MCR Guard has been battle tested in conflicts around the world and offers excellent permeation resistance to most acids, aldehydes, alcohols, amides, bases, esters, and ketones. These gloves are produced domestically with a unique solution dipped process. No other process can achieve such a tight molecular structure, the key to chemical impermeability. MCR Guard is made with the finest Butyl rubber for outstanding protection. The CP25 is a 25 mil smooth finish glove that features a rolled cuff that is 14 inches in length for added protection.

FEATURES:

- 25 mil Butyl Rubber
- Excellent Chemical Resistance
- 14 inch Gauntlet Cuff
- Smooth Finish
- Component materials comply with all federal regulations for food contact

APPLICATIONS:

First responder, Laboratory Technician, Aerospace, Agriculture, Biomedical, Food, HazMat, Petrochemical industries



TECHNICAL DATA FOR: CP25

Series	MCR Guard	Overall Length	14 in.
Material Group	Unsupported		
Product Type	Unsupported		
Glove Size	Large		
Material	Butyl		
Grade	Industrial Grade		
Features	Sold by pair		
Lining	Unlined		
Thumb Style	Wing		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

CP25

MCR Guard

Unsupported

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
CP25L	Large	14.25	5.76	N/A	33.192 lb.	0.461
CP25M	Medium	14.00	5.50	N/A	28.656 lb.	0.398
CP25S	Small	13.75	4.88	N/A	0.000 lb.	0.375
CP25XL	X - Large	15.00	6.76	N/A	32.976 lb.	0.458

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved