



MCR
SAFETY

9750 Predator

Supported / Dipped gloves Specification Sheet

PRODUCT DESCRIPTION:

The protection the Predator® gloves offer is unmatched in the market giving you the advantage over what you will face at work today. The 9750 Predator® features premium nitrile palm coating on a soft jersey liner treated with Actifresh. Comfortable knit wrist.

FEATURES:

- Premium Nitrile Coating
- Soft Jersey Lining
- Knit Wrist
- CE Score 4221

APPLICATIONS:

Oil and Gas Industry, Farming, Janitorial , Landscaping,
Material Handling



TECHNICAL DATA FOR: 9750

Series	Predator	Overall Length	11 in.
Material Group	Supported	EN 388 : CE Score - Abrasion	4
Product Type	Supported / Dipped gloves	EN 388 : CE Score - Cut	2
Glove Size	Large	EN 388 : CE Score - Tear	2
Material	Nitrile	EN 388 : CE Score - Puncture	1
Grade	Premium	FDA Accepted Materials	FDA Compliant
Lining	Jersey	ANSI Cut	ANSI Cut A2
Thumb Style	Straight		




MCR
SAFETY

9750

Predator

Supported / Dipped gloves
Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
9750	Large	10.827	6.379	3.000	36.336 lb.	3.028
9750S	Small	10.039	5.551	3.000	30.396 lb.	2.533

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved