

DEWALT[®]

GUARANTEED TOUGH[®]

MADE IN THE
USA
WITH GLOBAL MATERIALS

LOOK FOR THIS LOGO ON SPECIALLY
MARKED DEWALT PACKAGES.

**PERFORM
PROTECT[™]**

E-CLUTCH[®]

E-CLUTCH[®] SYSTEM

Activates in Less Than a Tenth
of a Second When a Pinch/Stall
Event is Detected.

HIGH POWER 13 AMP MOTOR

Powerful 1700 Watt Motor Offers
Lower Field Case Temperatures
to Improve Durability*

DUST EJECTION SYSTEM[™]

Contributes to Long Motor Life

**LANYARD
READY[™]**

LANYARD READY[™] Compatible

Lanyard Ready[™] Connection Point
Available as a Part Through Service
for No Lock-On Models Only

TWO STAGE TRIGGER

Requires Two Actions to
Activate Tool. Lock-On and
No Lock-On Versions Available.

ONE-TOUCH[™] COMPATIBLE GUARD

Simple Lever Change Allows Unit
to be One-Touch[™] or Two-Touch for
Guard Adjustments. Includes 5" and
6" Type 27 and 6" Type 1 Guards.

COMPATIBLE WITH

DUST



DWE46152
5" SURFACE GRINDING
DUST SHROUD



DWE46100
5" / 6" CUTTING &
TUCKPOINTING DUST
SHROUD

INCLUDES

- (1) 6" (150 mm) Type 27 Guard
- (1) 6" (150 mm) Type 1 Guard

*As compared to previous 13 Amp
DEWALT Small Angle Grinder Models

**5" (125 mm) / 6" (150 mm) HIGH PERFORMANCE
PADDLE SWITCH GRINDER WITH NO LOCK ON**

DWE43144N

SPECIFICATIONS | DWE43144N

Amps	13.0 AC Amps
Max Watts Out/ Max Horsepower	1,700 W/2.3HP
No Load Speed	9,000 RPM
Spindle Thread	5/8"-11
Switch Type	Paddle No Lock-on
Dust Ejection System	Yes
Tool-Free Flange System	Yes
E-Clutch® System/ Overload Protection	Yes
Tool Length (inches)	13
Tool Weight	6.2 lbs.
Power Loss Reset	Yes
Lanyard Ready™	Compatible*

TOOL WARRANTY

3
YEAR

LIMITED
WARRANTY

1
YEAR

FREE
SERVICE

90
DAY

MONEY BACK
GUARANTEE

RELATED PRODUCTS



6" (150MM) HIGH PERFORMANCE
PADDLE SWITCH GRINDER



4-1/2" (115MM)- 5" (125MM)
HIGH PERFORMANCE PADDLE
SWITCH GRINDER



4-1/2" (115MM)- 5" (125MM) HIGH
PERFORMANCE PADDLE SWITCH
GRINDER W/ NO LOCK ON



6" (150MM) NO LOCK PADDLE
CUTOFF TOOL WITH ADJUSTABLE
CUTOFF GUARD

SPECIFICATIONS	DWE43144	DWE43114	DWE43114N	DWE46144N
Amps	13.0 AC Amps	13.0 AC Amps	13.0 AC Amps	13.0 AC Amps
Max Watts Out/ Max Horsepower	1,700 W/2.3HP	1,700 W/2.3HP	1,700 W/2.3HP	1,700 W/2.3HP
No Load Speed	9,000 RPM	11,000 RPM	11,000 RPM	9,000 RPM
Spindle Thread	5/8"-11	5/8"-11	5/8"-11	5/8"-11
Switch Type	Paddle	Paddle	Paddle No Lock-on	Paddle No Lock-on
Dust Ejection System	Yes	Yes	Yes	Yes
Tool-Free Flange System	Yes	Yes	Yes	Yes
E-Clutch® System/ Overload Protection	Yes	Yes	Yes	Yes
Tool Length (inches)	13	13	13	16.5
Tool Weight	6.2 lbs.	5.5 lbs.	5.5 lbs.	6.8 lbs.
Power Loss Reset	Yes	Yes	Yes	Yes
Lanyard Ready™	No	No	Compatible*	Yes

*Lanyard Ready™ Connection Point Available as a Part Through Service for No Lock-On Models Only

Dealer Stamp

1-800-4DEWALT

www.DEWALT.com

Copyright ©2017 DeWALT. The following are examples of trademarks for one or more DeWALT power tools and accessories: the yellow and black color scheme; the "D"-shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.

ICDWE43144NSS