


**STRAIGHT GROUNDING CONDUIT AND CORD CONNECTORS****Straight Insulated Connector with Ground Lug, Steel/Malleable Iron  
N/A****B50**

Catalog #: 3512-3

**APPLICATIONS**

For use in outdoor or indoor locations on flexible metallic liquidtight conduit, when installation of a copper or aluminum external bonding jumper is required RACO grounding liquidtight connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

**PRODUCT FEATURES**

Patented split gland-ring is designed to slip onto the conduit quickly gripping the jacket of the conduit, speeding installation, assuring a perfect seal, and preventing pullouts  
 All components are reusable - RACO liquidtight connectors may be easily disassembled and reused after years of service  
 Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening  
 Heavy duty locknut included with every RACO liquidtight connector assures continuity of ground  
 All metallic components are zinc electro plated for added corrosion protection  
 3/8 in. to 1 in. Steel bodies; 1-1/4 in. to 4 in. Malleable Iron bodies  
 3/8 in. to 1 in. Steel nuts; 1-1/4 in. to 4 in. Malleable Iron nuts  
 N/A

**UL LISTED**

Standard 514B, UL Listed E195969

**CSA**

C22.2 No. 18

**GENERAL PRODUCT INFORMATION**

Trade Size: 1/2 in.  
 Min. Grounding Wire Capacity: #14 SOL.  
 Max Grounding Wire Capacity: #4 STR.

**DRAWING DIMENSIONS**

Dimension A: 1-3/16 in.  
 Dimension B: 1/2 in.  
 Thread Spec. B: 1/2 in. - 14 NPT  
 Dimension C: 1-15/32 in.  
 Dimension D: 25/32 in.

**PACKAGING**

Package Type: Carton  
 Ship Carton Qty.: 25  
 Product UPC-A Labeled: No  
 Weight (Lbs. Per/C): 21.80  
 Ship Carton Length (in.): 8.25  
 Ship Carton Width (in.): 5.00  
 Ship Carton Height (in.): 4.00  
 Ctn Weight (Lbs.): 5.45  
 UPC Number: 050169351239  
 I2of5: 50050169351234