


PVC, CPVC

TRUE UNION BALL VALVE

Features:

- Pressure rating: 225 PSI @ 73.4°F 1/2"~2"
- Pressure rating: 150 PSI @ 73.4°F 3"~4"
- Meets all applicable ASTM F-1970, D-2467 (Socket) & D-2466 (NPT), NSF-61
- Size from 1/2" to 4" in diameter
- Full port design
- Adjustable seat tightness
- Less on-line down time for replacement / maintenance
- Not recommended in compressed air or gas application.



Unit: Inch

Grainger #	Material	Size	Seat	O-ring	End type	H1	D	D1	d	d1	d2	L	L1	L2	I
4PGA5	PVC	1/2	PTFE	EPDM	Soc+NPT	1.850	1.830	1.220	0.502	0.848	0.836	4.488	2.362	3.071	0.875
4PGA6	PVC	3/4	PTFE	EPDM	Soc+NPT	2.244	2.165	1.456	0.698	1.058	1.046	5.314	2.874	3.622	1.000
4PGA7	PVC	1	PTFE	EPDM	Soc+NPT	2.598	2.598	1.771	0.911	1.325	1.310	5.866	3.110	3.937	1.125
4PGA8	PVC	1 1/4	PTFE	EPDM	Soc+NPT	2.913	3.228	2.126	1.227	1.670	1.655	6.614	3.464	4.330	1.250
4PGA9	PVC	1 1/2	PTFE	EPDM	Soc+NPT	3.425	3.858	2.559	1.446	1.912	1.894	6.889	3.740	4.763	1.375
4PGC1	PVC	2	PTFE	EPDM	Soc+NPT	4.173	4.724	3.110	1.861	2.387	2.369	8.188	4.488	5.787	1.500
4PGC2	PVC	3	PTFE	EPDM	Soc+NPT	5.118	6.417	4.251	2.820	3.516	3.492	11.968	6.220	8.818	1.875
4PGC3	PVC	4	PTFE	EPDM	Soc+NPT	7.007	8.858	5.748	3.737	4.518	4.491	13.070	6.929	10.944	2.250
4PGC4	CPVC	1/2	PTFE	EPDM	Soc+NPT	1.850	1.830	1.220	0.502	0.848	0.836	4.488	2.362	3.071	0.875
4PGC5	CPVC	3/4	PTFE	EPDM	Soc+NPT	2.244	2.165	1.456	0.698	1.058	1.046	5.314	2.874	3.622	1.000
4PGC6	CPVC	1	PTFE	EPDM	Soc+NPT	2.598	2.598	1.771	0.911	1.325	1.310	5.866	3.110	3.937	1.125
4PGC7	CPVC	1 1/4	PTFE	EPDM	Soc+NPT	2.913	3.228	2.126	1.227	1.670	1.655	6.614	3.464	4.330	1.250
4PGC8	CPVC	1 1/2	PTFE	EPDM	Soc+NPT	3.425	3.858	2.559	1.446	1.912	1.894	6.889	3.740	4.763	1.375
4PGC9	CPVC	2	PTFE	EPDM	Soc+NPT	4.173	4.724	3.110	1.861	2.387	2.369	8.188	4.488	5.787	1.500
4PGD1	CPVC	3	PTFE	EPDM	Soc+NPT	5.118	6.417	4.251	2.820	3.516	3.492	11.968	6.220	8.818	1.875
4PGD2	CPVC	4	PTFE	EPDM	Soc+NPT	7.007	8.858	5.748	3.737	4.518	4.491	13.070	6.929	10.944	2.250
4PGD3	PVC	1/2	PTFE	FPM	Soc+NPT	1.850	1.830	1.220	0.502	0.848	0.836	4.488	2.362	3.071	0.875
4PGD4	PVC	3/4	PTFE	FPM	Soc+NPT	2.244	2.165	1.456	0.698	1.058	1.046	5.314	2.874	3.622	1.000
4PGD5	PVC	1	PTFE	FPM	Soc+NPT	2.598	2.598	1.771	0.911	1.325	1.310	5.866	3.110	3.937	1.125
4PGD6	PVC	1 1/4	PTFE	FPM	Soc+NPT	2.913	3.228	2.126	1.227	1.670	1.655	6.614	3.464	4.330	1.250
4PGD7	PVC	1 1/2	PTFE	FPM	Soc+NPT	3.425	3.858	2.559	1.446	1.912	1.894	6.889	3.740	4.763	1.375
4PGD8	PVC	2	PTFE	FPM	Soc+NPT	4.173	4.724	3.110	1.861	2.387	2.369	8.188	4.488	5.787	1.500
4PGD9	PVC	3	PTFE	FPM	Soc+NPT	5.118	6.417	4.251	2.820	3.516	3.492	11.968	6.220	8.818	1.875
4PGE1	PVC	4	PTFE	FPM	Soc+NPT	7.007	8.858	5.748	3.737	4.518	4.491	13.070	6.929	10.944	2.250
4PGE2	CPVC	1/2	PTFE	FPM	Soc+NPT	1.850	1.830	1.220	0.502	0.848	0.836	4.488	2.362	3.071	0.875
4PGE3	CPVC	3/4	PTFE	FPM	Soc+NPT	2.244	2.165	1.456	0.698	1.058	1.046	5.314	2.874	3.622	1.000
4PGE4	CPVC	1	PTFE	FPM	Soc+NPT	2.598	2.598	1.771	0.911	1.325	1.310	5.866	3.110	3.937	1.125
4PGE5	CPVC	1 1/4	PTFE	FPM	Soc+NPT	2.913	3.228	2.126	1.227	1.670	1.655	6.614	3.464	4.330	1.250
4PGE6	CPVC	1 1/2	PTFE	FPM	Soc+NPT	3.425	3.858	2.559	1.446	1.912	1.894	6.889	3.740	4.763	1.375
4PGE7	CPVC	2	PTFE	FPM	Soc+NPT	4.173	4.724	3.110	1.861	2.387	2.369	8.188	4.488	5.787	1.500
4PGE8	CPVC	3	PTFE	FPM	Soc+NPT	5.118	6.417	4.251	2.820	3.516	3.492	11.968	6.220	8.818	1.875
4PGE9	CPVC	4	PTFE	FPM	Soc+NPT	7.007	8.858	5.748	3.737	4.518	4.491	13.070	6.929	10.944	2.250