



Cut

Durable polyurethane gloves with a lightweight liner, for flexibility and tactility

- **Heightened flexibility:** HyFlex® 11-731 polyurethane gloves' lightweight 18-gauge liner enhances flexibility and tactility
- **Enhanced durability:** These safety gloves' PU coating offers greater dexterity and makes them more abrasion-resistant, for EN level 4 and ANSI level 3 abrasion protection
- **Improved defenses:** HyFlex® 11-731 industrial safety gloves' INTERCEPT™ Cut Resistance Technology yarn grant them added lacerations defenses, with ISO B/ANSI A2 protection
- **Considered aesthetics:** Dirt-masking color treatment on these HyFlex gloves' coating hides stains and marks, ensuring longer glove life
- **Guaranteed convenience:** These PPE gloves are also available in vend pack form, for simplified access to personal protection



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Transportation

Applications

- Assembly & inspection of components
- Press injection molding
- Picking, fastening components
- Final assembly
- Delivery of parts to production line
- Applying finish to materials, products
- Handling incoming goods

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-731

Enhanced comfort, durability and
INTERCEPT® Cut Resistance
Technology

Key Features

- **Light 18-gauge liner:** Greater flexibility and tactile sensitivity
- **Thin PU coating:** Durable industrial gloves with strengthened grip
- **INTERCEPT™ Cut Resistance:** For reliable personal protection

Performance Standards & Regulatory Compliance

REACH Compliant



Technologies



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex® 11-731	Finishing: Palm Coated Coating Material: Polyurethane Liner Material: Fiber glass, HPPE, Nylon, Spandex Cuff Style: Knitwrist	18	6, 7, 8, 9, 10, 11	212-277 mm/ 8,34-10,43 inch	Grey	• 12 pairs/bag; 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jaijan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

