



Elastic cuff for a comfortable fit

Flexible sandy nitrile palm coating provides superior grip and abrasion resistance

Core9™ (13G HPPE, steel, and fiberglass blend) shell for industry-leading 360° cut resistance

High dexterity








Back-of-hand IR-X® Impact Exoskeleton™ with high-flex design provides ANSI/ISEA 138 Level 2 protection on knuckles and Level 1 protection on fingers

Launderable



2098 Thin Lizzie™

PROTECTION ZONES:

 Impact Protection	 Core9™ Shell			
		ANSI/ISEA CUT	GRAM SCORE	CE 
		A9	6437	4X44FP
		ANSI/ISEA 138	ANSI/ISEA PUNCTURE	
		 1	 5	

FEATURES:

The Rig Lizard® Series is purpose-built to provide maximum grip in tough situations – with over five grip options for water, oils, muds, and lubricants. Each glove is also equipped with our highly flexible IR-X® Impact Exoskeleton™, keeping hands protected from smash and pinch injuries. This combination of multiple technologies and features makes the Rig Lizard® the ideal solution for common oil, gas, and mining hazards. And with options for cold weather protection, your hands can stay safe and comfortable in any environment. The 2098 is made with a Core9™ technology shell that offers industry-leading, 360°, A9 cut protection and feels like a second skin without compromising durability.

ATTRIBUTES:

Style:	Seamless Coated
Grip:	Wet or dry
Cuff Style:	Elastic
Sizes:	5/XXS through 12/3XL

HexArmor®

Call 1-877-MY ARMOR or visit hexarmor.com

HexArmor® products are cut and puncture resistant, NOT CUT AND PUNCTURE PROOF. Do not use with moving or serrated blades or tools. User shall be exclusively responsible to assess the suitability of the product as specified for any individual application or use. Protection zones are to be used as a general guide. Actual product protection zones may differ. Product features, design, protection zones subject to change.

Protected by U.S. Patent No. D703,389