



# R-163

Durable impact protection with  
comfortable padded palm.



Impact Abrasion Protection Chemical Protection



Cut Vibration



Light Duty

## Impact protection with synthetic leather padded palm and touchscreen compatibility for comfort and ease-of-use.

The Ringers 163 Medium Duty Impact glove combines protection against impact hazards with enhanced durability and comfort due to a synthetic leather padded palm.

- Developed with Ringers' F3 Technology™ and patented TPR design for superior dexterity and comfort.
- Touchscreen compatible index, middle and thumb tips lessen the need to remove gloves.
- Hook and loop pull tab closure provides added security on the job.



### Industries

- Manufacturing
- Mining
- Oil and gas
- Automotive
- Automotive Aftermarket
- Recycling and Waste Disposal
- Emergency Medical Services
- Machinery and Equipment
- Utilities

### Applications

- General Purpose Auto Aftermarket
- Handling structural and body components
- Body painting including surface inspection
- Applying sealers, touching up
- Body panel repair and replacement
- Oil, fluids and filter change
- Engine transmission and repair
- Tire rotation & changes
- Seizing structural and body parts
- Equipment repair & maintenance
- Assembly and disassembly of equipment
- Final assembly
- Final inspection
- Operating of heavy machinery
- Hydraulic set and testing



## R-163

Durable impact protection with  
comfortable padded palm.

### Key Features

- TPR impact protection on top of hand and fingers
- Flexible knuckle TPR design with two detached fingers
- Durable synthetic leather palm for enhanced grip
- Padded palm for comfort
- Secure cuff closure with hook and loop rubber pull tab
- Reinforced thumb, index, and middle finger tips
- Wrap around index finger protecting wear and tear zone
- Touchscreen compatible index, middle and thumb tips

### Performance Standards & Regulatory Compliance

REACH Compliant



### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	COLOR	PACKAGE
RINGERS R163	Liner Material: N/A Cuff Style: Adjustable		11, 10, 12, 13, 7, 8, 9	Black	5 pairs/bag, 10 bags/carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306.  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending.  
[www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

**Ansell**

