



T-91™

Non-Solvent Degreaser



FEATURES

- Ideal for traditional solvent cleaning, plastic basin style part washers and dip tanks
- VOC compliant in all 50 states
- Zero VOCs: VOC's per CARB/OTC/ LADCO: 0 g/L, VOC content per SCAQMD: 0 g/L
- Biodegradable
- Efficient: requires less product than traditional solvents to get the job done
- pH = 8 - 9
- Contains no solvents
- Moderate foam for effective mechanical cleaning

APPLICATIONS

- Basin style parts washer
- Bilges
- Compressors
- Concrete
- Dip Tanks
- Drill presses
- Engines
- Floors
- Forklifts
- Grease traps
- Machinery
- Marine
- Tanks
- Tools

SPECIFICATIONS AND APPROVALS

- Canadian Food Inspection Agency • NSF International, A1

PROPERTIES

Appearance/physical state	Liquid
Odor	Mild soapy
Melting point/freezing point	Not available.
Boiling point/range	Not available
Vapor pressure	18 mm Hg
Partition coefficient	< 0
Percent volatile	85-87%
Flammability limit	Not established
Propellant	Not applicable
VOC Content	0 % per State and Federal Consumer Product Regulations
Color	Colourless to light yellow
Flash point	None
Density	8.67 lb/gal
Evaporation rate	1 BuAc (Water = 1)
Vapor density	Not established
Auto-ignition temperature	Not established
Viscosity	Not established
Specific Gravity (water=1)	1.03
Temperature Range °F(°C)	Not applicable
4-Ball Weld Load	Not applicable
Solubility (water)	100%

DIRECTIONS

(Trigger) Turn nozzle to spray or stream position. Pull trigger to spray. Then agitate surface with a brush cloth or wipe. Remove soils by wiping. Rinse with water for residue free surface. NOTE: Test for compatibility on sensitive materials. Do not heat above 175°F (79°C). Do not allow parts to soak longer than 24 hours. As a direct solvent degreaser replacement: Use T-91 undiluted (straight) as a direct solvent replacement for all heavy duty degreasing applications. Dilution Ratio Product: (as a neutral pH cleaner) Water Water Applications: (Suggested dilution ranges for cleaning surfaces not damaged by water alone)
 1:10 - 1:75 Floors: Light to Heavy Duty Cleaning/Degreasing
 Undiluted to 1 : 10 Metals: Heavy Duty Cleaning/Degreasing
 1:20 - 1:80 Plastics, rubbers & painted surfaces
 1:50 - 1:100 Glass
 1:10 - 1:80 Pressure Washing: Light to Heavy-Duty Cleaning/Degreasing
 1:10 - 1:25 Soak Tanks [Do Not Exceed 140°F (60°C)]

HANDLING

Observe good industrial hygiene practices

STORAGE

Store in original tightly closed container. Store away from incompatible materials (see Section 10 of the SDS).

DISPOSAL INFORMATION

Waste from residues / unused products: Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions). Contaminated packaging: Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.

AVAILABLE PRODUCTS

US	Part No.		Net Contents	Container Type	Units/Case	Case Weight
	Canada	Europe				
06328	C06328	M06328	28 fl oz / 828 mL	trigger	12	27 lbs
06301	C06301	M06301	1 gal / 3.78 L	bottles	4	38 lbs
06355	C06355	M06355	55 gal / 208 L	drum	1	535 lbs



CONTACT YOUR ITW PRO BRANDS REPRESENTATIVE TODAY!

800.241.8334 | www.itwprobrands.com

LPS®, SCRUBS®, DYKEM®, Accu-Lube®, DYMON®, Spray Nine®, and Cedar® are registered trademarks and Rustlick™, Diamondkote™, and MetalMates™ are trademarks of Illinois Tool Works • All Rights Reserved